



OCC1C compact CWDM, 8 channels + 1310 nm port, single demux, 1471 nm starting wavelength, SC/APC, 0.9 mm cable

## Product Classification

<b>Product Type</b>	CWDM component
<b>Product Series</b>	OCC1C
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## General Specifications

<b>Distribution Type</b>	8-channel CWDM
<b>Interface, input</b>	SC
<b>Interface, output</b>	SC
<b>Application</b>	For use in FOSC closures
<b>Circuits, quantity</b>	1
<b>Functionality</b>	Demultiplexing
<b>Interface Feature, input</b>	APC
<b>Interface Feature, output</b>	APC
<b>Multiplexers, quantity</b>	1
<b>Package, quantity</b>	1
<b>Port Type, optional</b>	1310 nm port   Tx and Rx test fibers
<b>Technology Type</b>	Free space optics

## Dimensions

<b>Pigtail Diameter</b>	0.90 mm   0.04 in
<b>Pigtail length, input</b>	2.50 m   8.20 ft
<b>Pigtail length, output</b>	2.50 m   8.20 ft

## Mechanical Specifications

<b>Device Type</b>	Component, rectangular
--------------------	------------------------

## Optical Specifications

<b>Starting Wavelength</b>	1471.00 nm
<b>Channel Spacing</b>	20 nm

## Regulatory Compliance/Certifications

**Agency**

**Classification**

RoHS 2011/65/EU

Compliant

