



OCC1C CWDM, double mux/demux, 1611 nm starting wavelength, 0.9 mm cable, field installable

Product Classification

| | |
|------------------------------|---|
| Product Type | CWDM component |
| Product Series | OCC1C |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

General Specifications

| | |
|-------------------------------|--------------------------|
| Distribution Type | 2-channel CWDM |
| Interface, input | Stub tail |
| Interface, output | Stub tail |
| Application | For use in FOSC closures |
| Circuits, quantity | 2 |
| Functionality | Multiplexing |
| Multiplexers, quantity | 2 |
| Package, quantity | 1 |
| Technology Type | Thin film filter (TFF) |

Dimensions

| | |
|-------------------------------|-------------------|
| Pigtail Diameter | 0.90 mm 0.04 in |
| Pigtail length, input | 2.50 m 8.20 ft |
| Pigtail length, output | 2.50 m 8.20 ft |

Mechanical Specifications

| | |
|--------------------|------------------------|
| Device Type | Component, rectangular |
|--------------------|------------------------|

Optical Specifications

| | |
|----------------------------|------------|
| Starting Wavelength | 1611.00 nm |
|----------------------------|------------|

Regulatory Compliance/Certifications

| | |
|---------------|-----------------|
| Agency | RoHS 2011/65/EU |
|---------------|-----------------|

| | |
|-----------------------|-----------|
| Classification | Compliant |
|-----------------------|-----------|

