



OCC1C CWDM, double mux/demux, 1471 nm starting wavelength, 0.9 mm cable, field installable

## Product Classification

<b>Product Type</b>	CWDM component
<b>Product Series</b>	OCC1C
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## General Specifications

<b>Distribution Type</b>	2-channel CWDM
<b>Interface, input</b>	Stub tail
<b>Interface, output</b>	Stub tail
<b>Application</b>	For use in FOSC closures
<b>Circuits, quantity</b>	2
<b>Functionality</b>	Multiplexing
<b>Multiplexers, quantity</b>	2
<b>Package, quantity</b>	1
<b>Technology Type</b>	Thin film filter (TFF)

## Dimensions

<b>Pigtail Diameter</b>	0.90 mm   0.04 in
<b>Pigtail length, input</b>	2.50 m   8.20 ft
<b>Pigtail length, output</b>	2.50 m   8.20 ft

## Mechanical Specifications

<b>Device Type</b>	Component, rectangular
--------------------	------------------------

## Optical Specifications

<b>Starting Wavelength</b>	1471.00 nm
----------------------------	------------

## Regulatory Compliance/Certifications

<b>Agency</b>	RoHS 2011/65/EU
---------------	-----------------

<b>Classification</b>	Compliant
-----------------------	-----------

