



FOSC™ A-TRAY-24 type, CWDM, 3 channels + upgrade port, double demux, 20 nm channel spacing, 1533.47 nm starting wavelength

## Product Classification

<b>Product Type</b>	CWDM splice tray
<b>Product Series</b>	FOSC-OC
<b>Product Brand</b>	FOSC™
<b>Regional Availability</b>	North America

## General Specifications

<b>Distribution Type</b>	3-channel CWDM
<b>Interface, input</b>	Stub tail
<b>Interface, output</b>	Stub tail
<b>Application</b>	For use in FOSC closures
<b>Circuits, quantity</b>	2
<b>Functionality</b>	Double demultiplexing
<b>Multiplexers, quantity</b>	2
<b>Package, quantity</b>	1
<b>Port Type, optional</b>	Upgrade port
<b>Technology Type</b>	Thin film filter (TFF)

## Dimensions

<b>Depth</b>	10.67 mm   0.42 in
<b>Height</b>	233.68 mm   9.20 in
<b>Width</b>	99.06 mm   3.90 in

## Mechanical Specifications

<b>Device Type</b>	FOSC splice tray
--------------------	------------------

## Optical Specifications

<b>Starting Wavelength</b>	1533.47 nm
<b>Channel Spacing</b>	20 nm

## Regulatory Compliance/Certifications

<b>Agency</b>	RoHS 2011/65/EU
---------------	-----------------

<b>Classification</b>	Compliant
-----------------------	-----------

