



Weatherproofing Kit for Connectors and Splices, includes butyl rubber and PVC tape

Product Classification

Product Type Weatherproofing tape

Dimensions

Nominal Size 0.195 in | 0.240 in | 0.300 in | 0.400 in | 0.600 in

General Specifications

Application Provides additional moisture seal for cable connections

Applications per Kit Four 0.195 in to 0.195 in | Four 0.240 in to 0.240 in | Three 0.300 in to 0.300 in | Three 0.400 in to 0.300 in | Three 0.400 in to 0.400 in | Two 0.400 in to 0.600 in | Two 0.600 in to 0.600 in

Includes One roll of 2-1/2 in butyl rubber tape (0.06 in thick) | One roll of 3/4 in PVC tape

Material Type Butyl rubber tape | PVC tape

Ordering Note CommScope® non-standard product

Package Quantity 1

Mechanical Specifications

UV Resistance Test Method Butyl test method in QUV weatherometer cycle of 8 hours UV at 150 °F then 4 hours of condensation at 104 °F | PVC tape test method UL 510, ASTM D1000

UV Resistance, minimum with no degradation =1000 hours

Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packed Dimensions

Height 16.5 cm | 6.5 in

Length 9.2 cm | 3.6 in

Shipping Weight 0.36 kg | 0.80 lb

Width 5.1 cm | 2.0 in

Regulatory Compliance/Certifications

WK-CNT

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



Included Products

42615-10 — Butyl Rubber Tape, 24 in

9905-41 — Black 3/4 in PVC Tape, 66 ft