

Double Block Hanger for 1/2 in coaxial cable (FSJ4)



Product Classification

Product Type Hanger kit

Dimensions

Nominal Size 1/2 in
Compatible Diameter, maximum 15.500 mm | 0.610 in
Compatible Diameter, minimum 13.500 mm | 0.531 in
Height 40.00 mm | 1.57 in
Length 67.00 mm | 2.64 in
Width 33.00 mm | 1.30 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Double block hanger
Cables per Hanger 2
Color Black
Material Type 30% glass filled polypropylene (PP)
Maximum Stack Height 3
Ordering Note CommScope® standard product in the United States and Canada
Package Quantity 10

Mechanical Specifications

Mounting Mounting hole clearance for 3/8, 16 UNC or M10 threaded rod
UV Resistance, minimum with no degradation =100 hours exposure in accelerated UV life chamber
Environmental Strength Capability Double cable weight

BHD-12S

Packed Dimensions

Height	3.8 cm 1.5 in
Length	25.4 cm 10.0 in
Shipping Weight	0.37 kg 0.81 lb
Width	17.8 cm 7.0 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power