



Furcation Tubing for Optical Fiber, indoor, no jacket, TPE tubing, 0.44/0.92 mm, black

- Protects optical fibers during and after the connector termination process
- Easy fiber insertion and wide variety of colors for fast fiber identification
- Low shrinkage and superior resistance to chemicals and temperature

## Product Classification

<b>Product Type</b>	Furcation tubing
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

<b>Inner Diameter, nominal</b>	0.440 mm   0.017 in
<b>Length</b>	14400.00 ft
<b>Outer Diameter, nominal</b>	0.920 mm   0.036 in
<b>Weight</b>	0.6 kg/km

## Environmental Specifications

<b>Environmental Space</b>	Indoor
<b>Installation Temperature</b>	-0 °C to +70 °C (-32 °F to +158 °F)
<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Storage Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)

## General Specifications

<b>Application</b>	For use with all fiber connector types   For use with singlemode and multimode optical fibers
<b>Color</b>	Black
<b>Package Quantity</b>	1
<b>Packaging Type</b>	Reel


## Material Specifications

<b>Material Type</b>	Elastomer   Thermoplastic polyester
----------------------	-------------------------------------

## Mechanical Specifications

<b>Minimum Bend Radius, Installation</b>	3.00 mm
<b>Minimum Bend Radius, Long Term</b>	5.00 mm
<b>Shrinkage, maximum</b>	0 ppm

## Outline Drawing



## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant

