



Standard Grounding Kit for 1-1/4 in corrugated coaxial cable and elliptical waveguide 64 and 77

OBSOLETE

Replaced By

241088-60

Standard Grounding Kit for 1-1/4 in corrugated coaxial cable and elliptical waveguide 64 and 77

Product Classification

Product Type Grounding kit

Dimensions

Nominal Size 1-1/4 in
Waveguide Size WR112 | WG15 | R84 | WR137 | WG14 | R70
Bonding Conductor Length 914.4 mm | 36 in
Cable Jacketing Removal Length, maximum 59.1 mm | 2.3 in
Cable Jacketing Removal Length, minimum 55.9 mm | 2.2 in
Compatible Diameter, maximum 40.132 mm | 1.580 in
Compatible Diameter, minimum 38.354 mm | 1.510 in

Electrical Specifications

Current Handling Tested to withstand 100,000 amps peak current surge
Current Handling Test Method MIL-STD-1757
Grounding, Bonding and Shielding Test Method MIL-STD-188-124A
Lightning Protection Test Method IEC 1024-1

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)
Storage Temperature -40 °C to +80 °C (-40 °F to +176 °F)
Weatherproofing Method Butyl and electric tape

General Specifications

Grounding Kit Type Standard Grounding Kits
Cable Type Corrugated | Elliptical waveguide
Ordering Note CommScope® non-standard product

Color	Black
Bonding Conductor Material	Copper
Bonding Conductor Wire Size	6 gauge
Bonding Conductor Jacketing Material	PVC
Grounding Strap Material	Copper
Includes	Grounding kit Hardware Lug One roll of 2 in PVC tape One roll of 24 in butyl rubber tape
Lug Attachment	Factory attached
Lug Type	Two-hole lug
Package Quantity	1
Rivet Material	Copper

Mechanical Specifications

Blowing Rain Test Method	MIL-STD-810, Method 506
Corrosion Test Method	MIL-STD-1344, Method 1001
Freezing Rain/Icing Test Method	MIL-STD-810, Method 521
Humidity Test Method	MIL-STD-1344, Method 1002
Immersion Test Method	IEC 60529:2001, IP68
Thread Size	3/8 in
UV Resistance Test Method	MIL-STD-810, Method 505
Vibration Test Method	MIL-STD-202, Method 214

Packed Dimensions

Height	266.7 mm 10.5 in
Length	57.2 mm 2.3 in
Shipping Weight	0.66 kg 1.46 lb
Width	177.8 mm 7.0 in

Included Products

9905-71 — Black 2 in PVC Tape, 20 ft

42615-10 — Butyl Rubber Tape, 24 in

* Footnotes

Grounding, Bonding and Shielding Test Method	Military Standard for Grounding, Bonding, and Shielding: Bond Resistance Requirement of a Maximum dc resistance of 0.001 ohm
Lightning Protection Test Method	Protection Against Lightning Electromagnetic Impulse, Table 1—Protection Level III–IV, 1995-02