



## SureGround® Compact Grounding Kit for 1/2 in corrugated coaxial cable

**OBSOLETE**

### Product Classification

<b>Brand</b>	SureGround®
<b>Product Type</b>	Grounding kit

### Dimensions

<b>Nominal Size</b>	1/2 in
<b>Bonding Conductor Length</b>	914.4 mm   36 in
<b>Cable Jacketing Removal Length, maximum</b>	59.1 mm   2.3 in
<b>Cable Jacketing Removal Length, minimum</b>	55.9 mm   2.2 in
<b>Compatible Diameter, maximum</b>	16.510 mm   0.650 in
<b>Compatible Diameter, minimum</b>	15.494 mm   0.610 in
<b>Enclosure Length</b>	121.9 mm   4.8 in
<b>Enclosure Width</b>	35.6 mm   1.4 in

### Electrical Specifications

<b>Current Handling</b>	Tested to withstand 100,000 amps peak current surge
<b>Current Handling Test Method</b>	MIL-STD-1757
<b>Grounding, Bonding and Shielding Test Method</b>	MIL-STD-188-124A
<b>Lightning Protection Test Method</b>	IEC 1024-1

### Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Storage Temperature</b>	-40 °C to +80 °C (-40 °F to +176 °F)
<b>Weatherproofing Method</b>	Copper strap contact overmolded with EPDM rubber

### General Specifications

<b>Grounding Kit Type</b>	Compact SureGround® Grounding Kits
<b>Cable Type</b>	Corrugated
<b>Ordering Note</b>	CommScope® non-standard product

<b>Color</b>	Black
<b>Bonding Conductor Material</b>	Copper
<b>Bonding Conductor Wire Size</b>	16 mm <sup>2</sup>
<b>Bonding Conductor Jacketing Material</b>	PVC
<b>Grounding Strap Material</b>	Copper
<b>Includes</b>	Grounding kit   Hardware   Lug
<b>Locking Bail Material</b>	Stainless steel
<b>Lug Attachment</b>	Factory attached
<b>Lug Type</b>	Two-hole lug
<b>Package Quantity</b>	1
<b>Rivet Material</b>	Copper

## Mechanical Specifications

<b>Blowing Rain Test Method</b>	MIL-STD-810, Method 506
<b>Corrosion Test Method</b>	MIL-STD-1344, Method 1001
<b>Freezing Rain/Icing Test Method</b>	MIL-STD-810, Method 521
<b>Humidity Test Method</b>	MIL-STD-1344, Method 1002
<b>Immersion Test Method</b>	IEC 60529:2001, IP68
<b>Thread Size</b>	3/8 in
<b>UV Resistance Test Method</b>	MIL-STD-810, Method 505
<b>Vibration Test Method</b>	MIL-STD-202, Method 214

## Packed Dimensions

<b>Height</b>	304.8 mm   12.0 in
<b>Length</b>	25.4 mm   1.0 in
<b>Shipping Weight</b>	0.36 kg   0.79 lb
<b>Width</b>	279.4 mm   11.0 in

## \* Footnotes

<b>Grounding, Bonding and Shielding Test Method</b>	Military Standard for Grounding, Bonding, and Shielding: Bond Resistance Requirement of a Maximum dc resistance of 0.001 ohm
<b>Lightning Protection Test Method</b>	Protection Against Lightning Electromagnetic Impulse, Table 1—Protection Level III–IV, 1995-02