



Double Hanger Kit for 7/8 in coaxial cable, triple stack; includes hardware and angle adapter

Product Classification

Brand	ValuSite™
Product Type	Hanger kit

Dimensions

Nominal Size	7/8 in
Compatible Diameter, maximum	28.194 mm 1.110 in
Compatible Diameter, minimum	26.670 mm 1.050 in
Height	20.70 cm 8.15 in
Length	3.77 cm 1.48 in
Width	2.61 cm 1.03 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

General Specifications

Hanger Type	Composite clamp
Cables per Hanger	6
Color	Black
Harmonized System (HS) Code	854420 (Coaxial cable and other coaxial electric conductors)
Includes	Angle adapter Hardware
Material Type	Engineered plastic Stainless steel
Maximum Stack Height	3
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa CommScope® standard product in Mexico, Central America, and South America

DHK-78-6-P

Package Quantity 1

Mechanical Specifications

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber
Mounting M8 hardware
UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber
Vibration Survival ≥4 hours at resonant frequency
Environmental Strength Capability Double cable weight

Packed Dimensions

Height 20.3 cm | 8.0 in
Length 15.2 cm | 6.0 in
Shipping Weight 0.27 kg | 0.60 lb

Included Products


Angle Adapter (Product Component—not orderable) — Angle Adapter

Hardware (Product Component—not orderable) — Hardware

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

Angle Adapter



Angle Adapter

Product Classification

Product Type Adapter

Dimensions

Inside Length 15.88 mm | 0.63 in

Inside Width 15.88 mm | 0.63 in

General Specifications

Adapter Type Angle adapter

Material Type Stainless steel

Ordering Note CommScope® non-standard product

Mechanical Specifications

Installation Torque, maximum 13.0 ft lb

Installation Torque, minimum 11.0 ft lb

Material Thickness 2.972 mm | 0.117 in

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

China RoHS SJ/T 11364-2014

Classification

Compliant

Above Maximum Concentration Value (MCV)



Hardware



Hardware

Product Classification

Product Type Hardware kit

Dimensions

Length 170.18 mm | 6.70 in

General Specifications

Includes Flat washers | Hex nuts | Lock washers | Threaded rod

Mechanical Specifications

Thread Size M8

Corrosion Resistance, minimum with no degradation ≥ 500 hours in salt spray chamber