

# BHD-12



## Double Block Hanger for 1/2 in coaxial cable (LDF4)

### Product Classification

**Product Type** Hanger kit

### Dimensions

<b>Nominal Size</b>	1/2 in
<b>Compatible Diameter, maximum</b>	16.256 mm   0.640 in
<b>Compatible Diameter, minimum</b>	15.494 mm   0.610 in
<b>Height</b>	40.00 mm   1.57 in
<b>Length</b>	67.00 mm   2.64 in
<b>Width</b>	33.00 mm   1.30 in

### Electrical Specifications

<b>DTF Effect</b>	0.1 dB
<b>Return Loss Effect</b>	0.1 dB

### Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

### General Specifications

<b>Hanger Type</b>	Double block hanger
<b>Cables per Hanger</b>	2
<b>Color</b>	Black
<b>Material Type</b>	30% glass filled polypropylene (PP)
<b>Maximum Stack Height</b>	3
<b>Ordering Note</b>	CommScope® standard product in the United States and Canada
<b>Package Quantity</b>	10

### Mechanical Specifications

**Mounting** Mounting hole clearance for 3/8, 16 UNC or M10 threaded rod

# BHD-12

---

**UV Resistance, minimum with no degradation** =100 hours exposure in accelerated UV life chamber

**Environmental Strength Capability** Double cable weight

## Packed Dimensions

<b>Height</b>	3.8 cm   1.5 in
<b>Length</b>	25.4 cm   10.0 in
<b>Shipping Weight</b>	0.37 kg   0.81 lb
<b>Width</b>	17.8 cm   7.0 in

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power