



Lace-up Hoisting Grip for 1/2 in coaxial cable and elliptical waveguide 180 and 220

Product Classification

Product Type Hoisting grip

Dimensions

Nominal Size 1/2 in
Grip Length, minimum 254.00 mm | 10.00 in
Leader Length, minimum 177.80 mm | 7.00 in

Electrical Specifications

DTF Effect 0.1 dB
Return Loss Effect 0.1 dB

General Specifications

Hoisting Grip Type Lace-up hoisting grip
Attachment Spacing Intervals 61 m | 200 ft
Material Type Stainless steel
Ordering Note CommScope® standard product in the United States and Canada
Package Quantity 1
Support Clamp Not included
Tool Type Hoisting grip

Mechanical Specifications

Pull Load Capacity 500 lb

Packed Dimensions

Height 4.2 cm | 1.7 in
Length 24.6 cm | 9.7 in
Width 18.8 cm | 7.4 in
Shipping Weight 0.20 kg | 0.44 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

