



FIST™ Splice Sub-assembly kit with 2 trays, each for holding up to 1 12-strip ribbon fiber, with Heat Shrink type splice holder

- Splice sub-assemblies consists of a wraparound groove plate holding the included splice organizer trays
- Groove plates are designed with slots for routing fiber to and from the organizer trays
- Loop-back facility allowing for single circuit uncut looped fiber storage on the splice tray
- Compliant with most splice types and independent of any optical fiber construction

Product Classification

| | |
|------------------------------|-------------------|
| Product Type | Fiber splice tray |
| Product Series | FIST-SOSA2 |
| Regional Availability | EMEA |
| Product Brand | FIST™ |


General Specifications

| | |
|---|--|
| Application | For use with BUDI fiber wall boxes For use with FIST fiber splice closures For use with FIST fiber splice panels |
| Color | Gray |
| Fiber Storage Length, maximum | 2050 mm for 12-ribbon fibers |
| Fiber Storage Length, minimum | 650.00 mm 25.59 in |
| Package, quantity | 1 |
| Packaging Type | Bag Carton |
| Splice Protector Diameter, maximum | 5.00 mm 0.20 in |
| Splice Protector Diameter, minimum | 3.50 mm 0.14 in |
| Splice Protector Length, maximum | 45.00 mm 1.77 in |
| Splice Protector Length, minimum | 35.00 mm 1.38 in |
| Splice Tray Chip Type | Heat shrink |
| Splice Tray Construction | R12 (for 1 ribbon 12 strip) |
| Splice Tray Included, quantity | 2 |
| Splices per Tray, note | 1 mass splice (12-ribbon) per tray |
| Splices per Tray, quantity | 1 |
| Used UMS Units, quantity | 3 |

Dimensions

| | |
|---------------|---------------------|
| Height | 12.00 mm 0.47 in |
| Length | 152.00 mm 5.98 in |
| Weight | 0.10 kg 0.22 lb |
| Width | 102.00 mm 4.02 in |

Dimension Drawing



Dimension Drawing Used as an image placeholder

Mechanical Specifications

Material Type PBT | PET
Minimum Bend Radius, standard 30.00 mm | 1.18 in

Environmental Specifications

Environmental Space Indoor | Outdoor
Relative Humidity 93%, non-condensing
Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant



* Footnotes

Used UMS Units, quantity The overall used splice tray height is expressed in UMS units. One UMS unit equals 6 mm.