



Jackmoon Fiber Optic Simplex Duct Plug, Size 1.50, for up to 1 cable with outer diameter between 22.9 and 27.9 mm

- Anchors and organizes subducts or multiple duct systems
- Eliminates duct-edge abrasion to cables
- Excellent for supporting cables at the tops of risers
- Expandable gasket allows for expansion and contraction of cables or subducts without leakage
- Split design for retrofitting without disassembly

## Product Classification

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Brand</b>                 | Jackmoon®                            |
| <b>Product Type</b>          | Duct plug, simplex fiber             |
| <b>Regional Availability</b> | EMEA   Latin America   North America |

## Dimensions

|  |          |
|--|----------|
| <b>Cable Diameter, maximum</b>         | 27.90 mm |
| <b>Cable Diameter, minimum</b>         | 22.90 mm |
| <b>Conduit Inner Diameter, maximum</b> | 43.90 mm |
| <b>Conduit Inner Diameter, minimum</b> | 40.10 mm |

## Environmental Specifications

|                                |                               |
|--------------------------------|-------------------------------|
| <b>Environmental Space</b>     | Handholes   Manholes          |
| <b>Qualification Standards</b> | IEC 60068-2-17, 5 m waterhead |

## General Specifications

|   |                           |
|---|---------------------------|
| <b>Application</b>                      | Cables   Pipes   Subducts |
| <b>Body Style</b>                       | Round                     |
| <b>Cables/Pipes Supported, quantity</b> | 1                         |
| <b>Color</b>                            | White                     |
| <b>Package Quantity</b>                 | 1                         |

## Material Specifications

|                      |     |
|----------------------|-----|
| <b>Material Type</b> | PVC |
|----------------------|-----|

## Regulatory Compliance/Certifications

|                 |                       |
|-----------------|-----------------------|
| <b>Agency</b>   | <b>Classification</b> |
| RoHS 2011/65/EU | Compliant             |

