



## PowerSUM M-Series Modular Jack, RJ45, Cat5e Unshielded, Blue

- Electrical performance guaranteed to meet or exceed the channel specifications to ISO/IEC 11801 Class E and ANSI/TIA-568.2-D Category 6
- Patented crossing of straddling pair contacts enables efficient alien crosstalk reduction in the channel
- Snaps into standard M-series faceplates, surface-mount boxes, consolidation point boxes and modular panels
- Mountable either at 90 degrees (straight) or 45 degrees (angled) in M-series faceplate
- Universal design and label supports both T568 A & B wiring
- IDC connector terminations on rear of base allow quick and easy installation of 22 to 24 AWG cable
- Can support network line speeds in excess of 1 Gb/s
- Low-profile rear protective strain relief cap, protects against contamination and secures the connection

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

### Portfolio

SYSTIMAX®

### Product Type

Modular jack

### Product Brand

PowerSUM

### Product Series

MPS100E

## General Specifications

### ANSI/TIA Category

5e

### Cable Type

Unshielded

### Color

Blue

### Conductor Type

Solid | Stranded

### Integrated Dust Cover Type

None

### Termination Type

IDC

### Wiring

T568A | T568B

## Dimensions

### Height

19.4 mm | 0.764 in

### Width

21.08 mm | 0.83 in

### Depth

30.2 mm | 1.189 in

# 760258932 | MPS100-BL

---

**Compatible Conductor Gauge, solid** 22 AWG | 24 AWG

**Compatible Conductor Gauge, stranded** 22 AWG | 24 AWG

## Electrical Specifications

**Contact Resistance Variation, maximum** 20 mOhm

**Contact Resistance, maximum** 100 mOhm

**Current Rating at Temperature** 1.5 A @ 20 °C | 1.5 A @ 68 °F

**Dielectric Withstand Voltage, RMS, conductive surface** 1,500 Vac @ 60 Hz

**Dielectric Withstand Voltage, RMS, contact-to-contact** 1,000 Vac @ 60 Hz

**Insulation Resistance, minimum** 500 MOhm

**Remote Powering** Fully supports the safe delivery of power over LAN cabling described by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002

**PoE Durability** Supports IEEE 802.3bt Type 4 (90 W) applications greater than 3000 plug to jack mating cycles

## Material Specifications

**Contact Plating Material** Precious metals

**Material Type** Copper alloy | High-impact, flame retardant, thermoplastic

**Termination Contact Plating** Nickel

## Mechanical Specifications

**Plug Retention Force, minimum** 133 N | 29.9 lbf

**Plug to Jack Mating Cycles** Complies to IEC 60603-7 series

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** Up to 95%, non-condensing

**Flammability Rating** UL 94 V-0

**Safety Standard** UL | cUL

## Packaging and Weights

**Packaging Material** Standard

# 760258932 | MPS100-BL

---

|                           |     |
|---------------------------|-----|
| <b>Packaging quantity</b> | 1   |
| <b>Packaging Type</b>     | Bag |