SFG23HDXL-13-4-126



G23HDXL PIM OPTIMIZED SPACING High Capacity Sector Frame . 2 7 /8in OD x 13ft face with (4) 2-7/8in OD x 126in Antenna pipes

Product Classification

Product Type High capacity Tower sector frame

Product Brand PIM-guard

Product Series G2

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

Patent Number For patents see: www.cs-pat.com

Pipe, quantity

Sectors, quantity

1

Tower Taper Non-tapered | Tapered

Dimensions

Height 3,200.4 mm | 126 in

Face Width 3.962 m | 13 ft

Platform Width3,962.4 mm| 156 inFace Support Pipe Diameter73.025 mm| 2.875 in

Mounting Diameter, maximum203.2 mm | 8 inMounting Diameter, minimum38.1 mm | 1.5 in

Pipe Outer Diameter73.025 mm | 2.875 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Wind Rating Test Method TIA/EIA-222-G



SFG23HDXL-13-4-126

Packaging and Weights

Included Frame | Plain end pipes (4) | Stiff arms (2) | Tower attachment

Packaging quantity 1

Weight, net 471.677 kg | 1,039.87 lb

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

