

SSH-12-4



SnapStak® Hanger for 1/2 in coaxial cable, quadruple stack capability, includes reinforcement bar

Product Classification

Product Type	Hanger kit
Product Brand	SnapStak®
Ordering Note	ANDREW® non-standard product

General Specifications

Cables per Hanger	1
Color	Silver
Hanger Type	Snap-in hanger
Mounting	3/4 in drilled cable ladder

Dimensions

Maximum Stack Height	4
Height	40.9 mm 1.61 in
Width	22.9 mm 0.902 in
Length	66 mm 2.598 in
Compatible Cable Diameter Range	15.5–18.3 mm
Compatible Diameter, maximum	18.3 mm 0.72 in
Compatible Diameter, minimum	15.5 mm 0.61 in
Nominal Size	1/2 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

SSH-12-4

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

Packaging and Weights

Height, packed 15.2 cm | 5.984 in

Width, packed 10.4 cm | 4.094 in

Length, packed 9 cm | 3.543 in

Packaging quantity 10

Weight, gross 0.36 kg | 0.794 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Included Products

SSHR-10 – SnapStak Hanger Reinforcement Bar, PIM free bar provides the ability to add an additional cable run to the stack

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

SSHR-10



SnapStak Hanger Reinforcement Bar, PIM free bar provides the ability to add an additional cable run to the stack

Product Classification

Product Type	Adapter
Product Brand	SnapStak®
Ordering Note	ANDREW® standard product in the United States and Canada

General Specifications

Accessories	Adapters
Color	Black
Mounting	3/4 in through hole

Dimensions

Height	76.2 mm 3 in
Width	25.4 mm 1 in
Length	6.35 mm 0.25 in

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Mechanical Specifications

Maximum Loading	Quadruple stack for SSH-M Triple stack for hangers SSH-XL, SSH-L Triple stack, 1-5/8 in cable
Vibration Survival	≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
UV Resistance, minimum with no degradation	≥1000 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	17 cm 6.693 in
-----------------------	------------------

SSHR-10

Width, packed	13 cm 5.118 in
Length, packed	10 cm 3.937 in
Packaging quantity	10
Weight, gross	0.15 kg 0.331 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

