760233361 | P-002-ZC-5G-F16LM



Fiber indoor cable, LazrSPEED® 1.6 mm Plenum Zipcord, Multimode OM5, Feet jacket marking, Lime green jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East/Africa | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series P-ZC

General Specifications

Cable Type Cordage

Construction Type Non-armored

Fiber Type, quantity 2

Jacket Color Lime green

Jacket Marking Feet

Subunit Type Gel-free

Total Fiber Count 2


Dimensions

Height Over Jacket1.7 mm | 0.067 inWidth Over Jacket3.5 mm | 0.138 in

Representative Image



760233361 | P-002-ZC-5G-F16LM



Mechanical Specifications

Minimum Bend Radius, loaded38 mm | 1.496 inMinimum Bend Radius, unloaded15 mm | 0.591 inTensile Load, long term, maximum53 N | 11.915 lbfTensile Load, short term, maximum178 N | 40.016 lbf

 Compression
 10 N/mm | 57.101 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 500 m | 1,640.42 ft

Optical Specifications

Fiber Type OM5, LazrSPEED® wideband | OM5, LazrSPEED® wideband

Environmental Specifications

Installation temperature 0 °C to +70 °C (+32 °F to +158 °F)

Page 2 of 6



760233361 | P-002-ZC-5G-F16LM

Operating Temperature $-20 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \left(-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F}\right)$

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFNP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

Environmental Test Specifications

Heat Age $-20 \,^{\circ}\text{C to} +85 \,^{\circ}\text{C} \left(-4 \,^{\circ}\text{F to} +185 \,^{\circ}\text{F}\right)$

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-20 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C } (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-20 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 6 kg/km | 4.032 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system
REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant



Included Products

CS-5G-TB - LazrSPEED® OM5 WideBand Multimode

Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



LazrSPEED® OM5 WideBand Multimode Fiber

LazrSPFFD®

Product Classification

PortfolioCommScope®Product TypeOptical fiber

General Specifications

Cladding Diameter 125 µm **Cladding Diameter Tolerance** ±0.8 µm Cladding Non-Circularity, maximum 0.7 % **Coating Diameter (Colored)** 254 µm **Coating Diameter (Uncolored)** 242 µm **Coating Diameter Tolerance (Colored)** ±7 µm **Coating Diameter Tolerance (Uncolored)** ±5 µm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 50 µm **Core Diameter Tolerance** ±2.5 µm Core/Clad Offset, maximum 1 µm

Proof Test 689.476 N/mm² | 100000 psi

Tight Buffer Diameter 900 μm Tight Buffer Diameter Tolerance $\pm 40 \ \mu m$

Mechanical Specifications

 Macrobending, 15 mm Ø mandrel, 2 turns
 0.20 dB @ 850 nm | 0.50 dB @ 1,300 nm

 Macrobending, 30 mm Ø mandrel, 2 turns
 0.10 dB @ 850 nm | 0.30 dB @ 1,300 nm

 Macrobending, 75 mm Ø mandrel, 100 turns
 0.50 dB @ 1,300 nm | 0.50 dB @ 850 nm

Coating Strip Force, maximum 4.5 N | 1.012 lbf



CS-5G-TB

Coating Strip Force, minimum 0.9 N | 0.202 lbf

Dynamic Fatigue Parameter, minimum 18

Optical Specifications

Numerical Aperture 0.2

Numerical Aperture Tolerance±0.010Point Defects, maximum0.15 dB

Zero Dispersion Slope, maximum (0M5) -412/(840(1-(λ0/840)^4)) ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum 1328 nm **Zero Dispersion Wavelength, minimum** 1297 nm

Optical Specifications, Wavelength Specific

1 Gbps Ethernet Distance 1,110 m @ 850 nm | 600 m @ 1,300 nm

10 Gbps Ethernet Distance 550 m @ 850 nm

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 2.20 dB/km @ 953 nm | 3.00 dB/km @

850 nm

Bandwidth, Laser, minimum 2,600 MHz-km @ 953 nm | 4,700 MHz-km @ 850 nm | 500 MHz-km

@ 1,300 nm

Bandwidth, OFL, minimum 1,950 MHz-km @ 953 nm | 3,500 MHz-km @ 850 nm | 500 MHz-km

@ 1,300 nm

Index of Refraction 1.478 @ 1,300 nm | 1.483 @ 850 nm

Standards Compliance ANSI/TIA-568.3-D wideband multimode fiber cable | IEC 60793-2-10,

edition 6, model A1a.4 | ISO 11801-1 cabled optical fiber performance

category OM5 | TIA-492AAAE (OM5)

Environmental Specifications

Heat Aging, maximum 0.10 dB/km @ 85 °C

Temperature Dependence, maximum0.1 dB/kmTemperature Humidity Cycling, maximum0.1 dB/km

Water Immersion, maximum 0.10 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



COMMSCOPE®

CS-5G-TB

* Footnotes

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

