



Fiber indoor/outdoor cable, LazrSPEED®, Single Jacket All-Dielectric, Low Smoke Zero Halogen (LSZH), 48 fiber, Multimode OM5, Gel-Free, Stranded Loose Tube, Black jacket color, Feet jacket marking, Cca flame rating

OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Europe Latin America North America
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	C-LN

General Specifications

Cable Type	Stranded loose tube
Construction Type	Non-armored
Subunit Type	Gel-free
Filler, quantity	1
Jacket Color	Black
Jacket Marking	Feet
Subunit, quantity	4
Fibers per Subunit, quantity	12
Total Fiber Count	48

Dimensions

Buffer Tube/Subunit Diameter	2.5 mm 0.098 in
Diameter Over Jacket	11.7 mm 0.461 in

Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded	175 mm 6.89 in
Minimum Bend Radius, unloaded	117 mm 4.606 in
Tensile Load, long term, maximum	800 N 179.847 lbf
Tensile Load, short term, maximum	2700 N 606.984 lbf
Compression	22 N/mm 125.623 lb/in
Compression Test Method	FOTP-41 IEC 60794-1 E3
Flex	25 cycles
Flex Test Method	FOTP-104 IEC 60794-1 E6
Impact	3 N-m 26.552 in lb
Impact Test Method	FOTP-25 IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1 E7
Vertical Rise, maximum	654 m 2,145.669 ft

Optical Specifications

Fiber Type	OM5, LazrSPEED® wideband OM5, LazrSPEED® wideband
------------	---

Environmental Specifications

Installation temperature	-30 °C to +55 °C (-22 °F to +131 °F)
Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)

760242812 | C-048-LN-5G-F12BK/25D/C

Storage Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Cable Qualification Standards	ANSI/ICEA S-104-696 EN 187105 Telcordia GR-20 Telcordia GR-409
EN50575 CPR Cable EuroClass Fire Performance	Cca
EN50575 CPR Cable EuroClass Smoke Rating	s1a
EN50575 CPR Cable EuroClass Droplets Rating	d0
EN50575 CPR Cable EuroClass Acidity Rating	a1
Environmental Space	Aerial, lashed Buried Low Smoke Zero Halogen (LSZH)
Flame Test Listing	EN 50399
Flame Test Method	EN 50399 IEC 60332-1 IEC 60754-2 IEC 61034-2
Jacket UV Resistance	UV stabilized
Water Penetration	24 h
Water Penetration Test Method	FOTP-82 IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze	-2 °C 28.4 °F
Cable Freeze Test Method	FOTP-98 IEC 60794-1 F15
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-30 °C to +55 °C (-22 °F to +131 °F)
Low High Bend Test Method	FOTP-37 IEC 60794-1 E11
Temperature Cycle	-40 °C to +60 °C (-40 °F to +140 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1 F1

Packaging and Weights

Cable weight	125 kg/km 83.996 lb/kft
--------------	---------------------------

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

CS-5G-LT

- - LazrSPEED® OM5 WideBand Multimode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable