


HL4RP-50A



ANDREW-Proprietary and Confidential. Preliminary specifications are for illustrative purposes only and will be updated prior to publication.

HL4-50A, HELIAX® Plenum Rated Air Dielectric Coaxial Cable, corrugated copper, 1/2 in, PVDF jacket

Product Classification

Product Type	Air coaxial cable
Product Brand	HELIAX®
Product Series	HL4-50A

General Specifications

Flexibility	Standard
Jacket Color	White
Performance Note	Values typical, guaranteed within 5% Values typical, unless otherwise stated

Dimensions

Diameter Over Jacket	15.367 mm 0.605 in
Inner Conductor OD	4.801 mm 0.189 in
Outer Conductor OD	13.843 mm 0.545 in
Nominal Size	1/2 in

Electrical Specifications

Cable Impedance	50 ohm \pm 2 ohm
Capacitance	75.459 pF/m 23 pF/ft
dc Resistance, Inner Conductor	1.476 ohms/km 0.45 ohms/kft
dc Resistance, Outer Conductor	1.903 ohms/km 0.58 ohms/kft
dc Test Voltage	4000 V
Inductance	0.19 μ H/m 0.058 μ H/ft
Insulation Resistance	100000 MOhms-km
Jacket Spark Test Voltage (rms)	5000 V

HL4RP-50A

Operating Frequency Band	1 – 8800 MHz
Peak Power	40 kW
Power Attenuation	2.325
Pulse Reflection	0.5%
Velocity	88 %

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
800–960 MHz	1.252	19.02
1700–2200 MHz	1.252	19.02

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.211	0.064	36.18
1.5	0.259	0.079	29.51
2.0	0.299	0.091	25.54
10.0	0.673	0.205	11.34
20.0	0.957	0.292	7.97
30.0	1.177	0.359	6.48
50.0	1.529	0.466	4.99
85.0	2.011	0.613	3.79
88.0	2.048	0.624	3.73
100.0	2.188	0.667	3.49
108.0	2.278	0.694	3.35
150.0	2.705	0.824	2.82
174.0	2.924	0.891	2.61
200.0	3.147	0.959	2.42
204.0	3.18	0.969	2.4
300.0	3.903	1.19	1.95
400.0	4.554	1.388	1.68
450.0	4.853	1.479	1.57
460.0	4.911	1.497	1.55
500.0	5.138	1.566	1.48
512.0	5.205	1.586	1.47
600.0	5.675	1.73	1.34

HL4RP-50A

700.0	6.176	1.882	1.24
800.0	6.648	2.026	1.15
824.0	6.758	2.06	1.13
894.0	7.07	2.155	1.08
960.0	7.357	2.242	1.04
1000.0	7.526	2.294	1.01
1218.0	8.407	2.562	0.91
1250.0	8.531	2.6	0.89
1500.0	9.461	2.884	0.81
1700.0	10.164	3.098	0.75
1794.0	10.483	3.195	0.73
1800.0	10.503	3.201	0.73
2000.0	11.163	3.402	0.68
2100.0	11.483	3.5	0.66
2200.0	11.798	3.596	0.65
2300.0	12.108	3.69	0.63
2500.0	12.714	3.875	0.6
2700.0	13.303	4.055	0.57
3000.0	14.159	4.315	0.54
3400.0	15.256	4.65	0.5
3600.0	15.788	4.812	0.48
3700.0	16.051	4.892	0.48
3800.0	16.311	4.971	0.47
3900.0	16.568	5.05	0.46
4000.0	16.824	5.128	0.45
4100.0	17.078	5.205	0.45
4200.0	17.329	5.282	0.44
4300.0	17.579	5.358	0.43
4400.0	17.827	5.433	0.43
4500.0	18.073	5.508	0.42
4600.0	18.317	5.583	0.42
4700.0	18.559	5.657	0.41
4800.0	18.8	5.73	0.41
4900.0	19.04	5.803	0.4
5000.0	19.277	5.875	0.4

HL4RP-50A

6000.0	21.581	6.577	0.35
8000.0	25.869	7.884	0.29
8800.0	27.494	8.38	0.28

Material Specifications

Dielectric Material	PE spline
Jacket Material	PVDF
Inner Conductor Material	Copper-clad aluminum wire
Outer Conductor Material	Corrugated copper

Mechanical Specifications

Minimum Bend Radius, multiple Bends	127 mm 5 in
Number of Bends, minimum	15
Number of Bends, typical	25
Tensile Strength	113 kg 249.122 lb
Bending Moment	4 ft lb 5.423 N-m
Flat Plate Crush Strength	1.429 kg/mm 80 lb/in

Environmental Specifications

Installation temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Operating Temperature	-20 °C to +80 °C (-4 °F to +176 °F)
Storage Temperature	-20 °C to +85 °C (-4 °F to +185 °F)
Attenuation, Ambient Temperature	68 °F 20 °C
Average Power, Ambient Temperature	104 °F 40 °C
Average Power, Inner Conductor Temperature	212 °F 100 °C
Fire Retardancy Test Method	NFPA 262/CATVP/CMP

Packaging and Weights

Cable weight	0.253 kg/m 0.17 lb/ft
---------------------	-------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
UL/ETL Certification	CATVP

HL4RP-50A

