

# RCT7-CPUS-4A-AXA



RCT7, RADIAX® Coaxial Radiating Cable with Bump, 50–2400 MHz, tuned foil, 1-5/8 in, black PE jacket

## OBSOLETE

This product was discontinued on: February 29, 2012

### Replaced By:

RCT7-CPUS-4A-RNA	RCT7, RADIAX® Coaxial Radiating Cable with Bump, 50–2400 MHz, tuned foil, 1-5/8 in, black non-halogenated, fire retardant polyolefin jacket
RCT7-CPUS-4A-RNAM	RCT7, RADIAX® Coaxial Radiating Cable with Bump, 50–2400 MHz, tuned foil, 1-5/8 in, black non-halogenated, fire retardant polyolefin jacket
RCT7-CPUS-4A-RVD	RCT7, RADIAX® Coaxial Radiating Cable with Bump, 50–2400 MHz, tuned foil, 1-5/8 in, black non-halogenated, fire retardant polyolefin jacket
RCT7-CPUS-5A-RNA	RCT7, RADIAX® Coaxial Radiating Cable with Bump, 50–2700 MHz, tuned foil, 1-5/8 in, black non-halogenated, fire retardant polyolefin jacket (For Hong Kong XRL 850 project only)
RCT7-TCP-1A-RNA	RCT7, RADIAX® Coaxial Radiating Cable with Bump, 380–1880 MHz, tuned foil, 1-5/8 in, black non-halogenated, fire retardant polyolefin jacket

## Product Classification

<b>Product Type</b>	Radiating cable
<b>Product Brand</b>	RADIAX®
<b>Product Series</b>	RCT7

## General Specifications

<b>Polarization</b>	Vertical
<b>Cable Type</b>	Radiating Mode (RCT) Series
<b>Jacket Color</b>	Black

## Dimensions

<b>Diameter Over Jacket, maximum</b>	49.784 mm   1.96 in
--------------------------------------	---------------------

# RCT7-CPUS-4A-AXA

<b>Inner Conductor OD</b>	18.161 mm   0.715 in
<b>Outer Conductor OD</b>	43.815 mm   1.725 in
<b>Nominal Size</b>	1-5/8 in
<b>Recommended Distance from the Wall</b>	101.6 mm   4 in
<b>Recommended Hanger Spacing</b>	1.3 m   4.265 ft

## Electrical Specifications

<b>Attenuation Test Method</b>	IEC 61196-4
<b>Attenuation Tolerance</b>	±5%
<b>Cable Impedance</b>	50 ohm ±2 ohm
<b>dc Resistance, Inner Conductor</b>	1.435 ohms/km   0.437 ohms/kft
<b>dc Resistance, Outer Conductor</b>	1.969 ohms/km   0.6 ohms/kft
<b>dc Test Voltage</b>	15000 V
<b>Insulation Resistance</b>	100000 MOhms-km
<b>Jacket Spark Test Voltage (rms)</b>	10000 V
<b>Operating Frequency Band</b>	50 – 2400 MHz
<b>Optimum Operating Frequency Band</b>	1700 – 2400 MHz   800 – 960 MHz
<b>Peak Power</b>	302 kW
<b>Stop Bands</b>	1110 – 1650 MHz
<b>Velocity</b>	93 %
<b>VSWR Installed, typical, 1700–2700 MHz</b>	1.38
<b>VSWR Installed, typical, 50–960 MHz</b>	1.3
<b>VSWR on Reel, typical</b>	1.43

## Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Coupling Loss 50%	Coupling Loss 95%
75.0	0.5	0.15	69	80
100.0	0.6	0.18	70	79
150.0	0.7	0.21	77	86
350.0	1.1	0.34	86	97
450.0	1.3	0.4	88	100
700.0	1.6	0.49	87	98
800.0	1.9	0.58	65	68
900.0	2.2	0.67	61	63

# RCT7-CPUS-4A-AXA

1700.0	6	1.83	51	53
1800.0	5.2	1.58	53	55
1900.0	4.8	1.46	55	57
2000.0	4.8	1.46	55	57
2100.0	4.6	1.4	56	58
2200.0	4.6	1.4	60	64
2300.0	4.7	1.43	59	65
2400.0	4.6	1.4	60	70

## Material Specifications

<b>Dielectric Material</b>	Foam PE
<b>Jacket Material</b>	PE
<b>Inner Conductor Material</b>	Corrugated copper tube
<b>Outer Conductor Material</b>	Copper foil

## Mechanical Specifications

<b>Minimum Bend Radius, single Bend</b>	508 mm   20 in
<b>Tensile Strength</b>	215 kg   473.993 lb
<b>Bending Moment</b>	16 N-m   141.612 in lb
<b>Coupling Loss Test Method</b>	IEC 61196-4
<b>Coupling Loss Tolerance</b>	±5 dB
<b>Flat Plate Crush Strength</b>	0.8 kg/mm   44.798 lb/in
<b>Indication of Slot Alignment</b>	Yes—bumps face the wall

## Environmental Specifications

<b>Installation temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Operating Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)
<b>Storage Temperature</b>	-70 °C to +85 °C (-94 °F to +185 °F)
<b>Attenuation, Ambient Temperature</b>	68 °F   20 °C
<b>Average Power, Ambient Temperature</b>	104 °F   40 °C
<b>Average Power, Inner Conductor Temperature</b>	212 °F   100 °C
<b>Toxicity Index Test Method</b>	IEC 60754-1   IEC 60754-2

## Packaging and Weights

# RCT7-CPUS-4A-AXA

---

**Cable weight**

0.6 kg/m | 0.403 lb/ft

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

