

AVA6-50, HELIAX® Andrew Virtual Air™ Coaxial Cable, corrugated copper, 1-1/4 in, black PE jacket (Halogen free jacketing non-fire-retardant)

Product Classification

Product Type	Coaxial wireless cable
Product Brand	HELIAX®
Product Series	AVA6-50
Ordering Note	North America alternative part number is AVA6P-50-C (520092002 /00) Not available in the United States or Canada
General Specifications	
Product Number	520097802/00 SZ520097802/00
Flexibility	Standard
Jacket Color	Black
Performance Note	Attenuation values typical, guaranteed within 5%
Dimensions	
Diameter Over Dielectric	34.036 mm 1.34 in
Diameter Over Jacket	39.624 mm 1.56 in
Inner Conductor OD	14.021 mm 0.552 in
Outer Conductor OD	36.068 mm 1.42 in
Nominal Size	1-1/4 in
Electrical Specifications	
Cable Impedance	50 ohm ±1 ohm
Capacitance	72 pF/m 21.946 pF/ft
dc Resistance, Inner Conductor	1.74 ohms/km 0.53 ohms/kft
dc Resistance, Outer Conductor	0.75 ohms/km 0.229 ohms/kft
dc Test Voltage	8500 V
Inductance	0.187 μH/m 0.057 μH/ft
Insulation Resistance	100000 MOhms-km

Page 1 of 4

©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

AVA6-50

Jacket Spark Test Voltage (rms)	10000 V
Operating Frequency Band	1 – 4000 MHz
Peak Power	180 kW
Velocity	92 %

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
680-800 MHz	1.13	24.3
806–960 MHz	1.13	24.3
1700–2170 MHz	1.13	24.3

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.079	0.024	82.63
1.5	0.097	0.03	67.41
2.0	0.113	0.034	58.33
10.0	0.253	0.077	25.89
20.0	0.36	0.11	18.21
30.0	0.443	0.135	14.8
50.0	0.576	0.176	11.39
85.0	0.758	0.231	8.66
88.0	0.772	0.235	8.51
100.0	0.825	0.251	7.96
108.0	0.858	0.262	7.65
150.0	1.019	0.311	6.44
174.0	1.102	0.336	5.96
200.0	1.186	0.361	5.53
204.0	1.198	0.365	5.48
300.0	1.471	0.448	4.46
400.0	1.717	0.523	3.82
450.0	1.829	0.558	3.59
460.0	1.851	0.564	3.54
500.0	1.937	0.59	3.39
512.0	1.962	0.598	3.34
600.0	2.14	0.652	3.07

©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

Page 2 of 4



AVA6-50

700.0	2.329	0.71	2.82
800.0	2.507	0.764	2.62
824.0	2.548	0.777	2.58
894.0	2.666	0.813	2.46
960.0	2.774	0.846	2.37
1000.0	2.838	0.865	2.31
1218.0	3.171	0.967	2.07
1250.0	3.218	0.981	2.04
1500.0	3.569	1.088	1.84
1700.0	3.835	1.169	1.71
1794.0	3.955	1.206	1.66
1800.0	3.963	1.208	1.66
2000.0	4.212	1.284	1.56
2100.0	4.333	1.321	1.51
2200.0	4.452	1.357	1.47
2300.0	4.569	1.393	1.44
2500.0	4.798	1.462	1.37
2700.0	5.021	1.53	1.31
3000.0	5.345	1.629	1.23
3400.0	5.76	1.755	1.14
3600.0	5.961	1.817	1.1
3700.0	6.06	1.847	1.08
3800.0	6.16	1.877	1.07
4000.0	6.36	1.94	1.03

Material Specifications

Dielectric Material	Foam PE
Jacket Material	PE
Inner Conductor Material	Corrugated copper tube
Outer Conductor Material	Corrugated copper

Mechanical Specifications

Minimum Bend Radius, multiple Bends	203.2 mm 8 in
Minimum Bend Radius, single Bend	152.4 mm 6 in
Number of Bends, minimum	15

Page 3 of 4



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

AVA6-50

Number of Bends, typical	40
Tensile Strength	154 kg 339.511 lb
Bending Moment	29.8 N-m 263.752 in lb
Flat Plate Crush Strength	1.3 kg/mm 72.797 lb/in

Environmental Specifications

Installation temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-70 °C to +85 °C (-94 °F to +185 °F)
Attenuation, Ambient Temperature	68 °F 20 °C
Average Power, Ambient Temperature	104 °F 40 °C
Average Power, Inner Conductor Temperature	212 °F 100 °C

Packaging and Weights

Cable weight

0.68 kg/m | 0.457 lb/ft

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 4 of 4



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025