

F187CCA2



FlexTwist® Flexible Twist for WR187, 4.4–5.0 GHz, with interface types CPR187G and CPR187G, 600 mm

Product Classification

| | |
|----------------------|---------------------------------------|
| Product Type | Rectangular waveguide, flexible twist |
| Product Brand | FlexTwist® |

General Specifications

| | |
|--------------------|----------------|
| Component | Flexible Twist |
| Interface | CPR187G |
| Interface 2 | CPR187G |

Dimensions

| | |
|-----------------------|--------------------|
| Length | 600 mm 23.622 in |
| Waveguide Size | WR187 WG12 R48 |

Electrical Specifications

| | |
|---------------------------------|-------------------------|
| Attenuation | 0.17 dB/m 0.052 dB/ft |
| Average Power | 3000 W |
| Operating Frequency Band | 4.4 – 5.0 GHz |
| Peak Power | 1250 kW |
| VSWR | 1.03 |

Mechanical Specifications

| | |
|--|----------------------------------|
| Minimum Bend Radius, Multiple Bends (E Plane) | 165 mm 6.496 in |
| Minimum Bend Radius, Multiple Bends (H Plane) | 330 mm 12.992 in |
| Maximum Twist | 165 °/m 50.292 °/ft |
| Pressurization, maximum | 0.207 N/mm ² 30 psi |

Regulatory Compliance/Certifications

F187CCA2

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS



Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant