

530092703 | P3® 750 JCAT G

75 Ohm P3® Trunk and Distribution Cable, black PE jacket with co-extruded blue stripes



Product Classification

Product Type	Coaxial hardline cable
Product Brand	P3®
Warranty	One year

General Specifications

Cable Type	750 Series
Construction Type	Swaged
Jacket Color	Black with co-extruded green stripe
Short Description	P3 750 JCAT B SM PR2171

Dimensions

Cable Length	762 m 2500 ft
Diameter Over Center Conductor, nominal	4.242 mm 0.167 in
Diameter Over Dielectric, nominal	17.323 mm 0.682 in
Diameter Over Jacket, nominal	20.828 mm 0.82 in
Diameter Over Outer Conductor, nominal	19.05 mm 0.75 in
Jacket Thickness, nominal	0.889 mm 0.035 in
Outer Conductor Thickness, nominal	0.864 mm 0.034 in

Electrical Specifications

Capacitance	50.197 pF/m 15.3 pF/ft
Capacitance Tolerance	±1.0 pF/ft
Characteristic Impedance	75 ohm
Characteristic Impedance Tolerance	±2 ohm

530092703 | P3® 750 JCAT G

dc Resistance Note	Nominal values based on a standard condition of 20 °C (68 °F)
dc Resistance, Inner Conductor, nominal	1.87 ohms/km 0.57 ohms/kft
dc Resistance, Loop, nominal	2.493 ohms/km 0.76 ohms/kft
dc Resistance, Outer Conductor, nominal	0.623 ohms/km 0.19 ohms/kft
Jacket Spark Test Voltage	5000 Vac
Nominal Velocity of Propagation (NVP)	87 %
Operating Frequency Band	5–3000 MHz
Structural Return Loss	24 dB @ 1003–1218 MHz 24 dB @ 1219–1794 MHz 30 dB @ 5–1002 MHz
Structural Return Loss, Grade N	≥24 dB @ 1003–1218 MHz ≥24 dB @ 1219–1794 MHz ≥30 dB @ 5–1002 MHz

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.36	0.11
55.0	1.21	0.37
85.0	1.51	0.46
204.0	2.36	0.72
211.0	2.43	0.74
250.0	2.66	0.81
300.0	2.92	0.89
350.0	3.18	0.97
400.0	3.44	1.05
450.0	3.67	1.12
500.0	3.87	1.18
550.0	4.07	1.24
600.0	4.3	1.31
750.0	4.86	1.48
865.0	5.28	1.61
1002.0	5.72	1.74
1218.0	6.41	1.95
1500.0	7.3	2.23
1794.0	8.07	2.46
1800.0	8.08	2.46
2000.0	8.57	2.61

530092703 | P3® 750 JCAT G

2200.0	9.05	2.76
2500.0	9.73	2.96
2700.0	10.16	3.1
3000.0	10.8	3.29

Material Specifications

Center Conductor Material	Copper-clad aluminum
Dielectric Material	Foam PE
Jacket Material	PE
Outer Conductor Material	Aluminum

Mechanical Specifications

Minimum Bend Radius, bonded	152.4 mm 6 in
Pulling Tension, maximum	306.175 kg 675 lb

Environmental Specifications

Environmental Space	Aerial
----------------------------	--------

Packaging and Weights

Packaging Type	Reel
Weight, gross	386.923 kg/km 260 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

