

# 2-599164-4 | C-012-CN-8W-M12YL/AY

Fiber Indoor/Outdoor Cable, 12-fiber, singlemode G.652.D and G.657.A1, Gel-filled, yellow jacket color, Eca Flame Rating, Meters jacket marking, 2000 meters

## OBSOLETE

This product was discontinued on: March 31, 2023

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Product Series</b>	C-CN

## General Specifications

<b>Cable Type</b>	Loose tube
<b>Subunit Type</b>	Gel-filled
<b>Jacket Color</b>	Yellow
<b>Jacket Marking</b>	Meters
<b>Fibers per Subunit, quantity</b>	12
<b>Total Fiber Count</b>	12

## Dimensions

<b>Cable Length</b>	2000 m   6,561.68 ft
<b>Diameter Over Jacket</b>	6.4 mm   0.252 in

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	140 mm   5.512 in
<b>Minimum Bend Radius, unloaded</b>	130 mm   5.118 in
<b>Tensile Load, long term, maximum</b>	400 N   89.924 lbf
<b>Tensile Load, short term, maximum</b>	500 N   112.404 lbf

## Optical Specifications

<b>Fiber Type</b>	G.652.D and G.657.A1
-------------------	----------------------

# 2-599164-4 | C-012-CN-8W-M12YL/AY

---

## Optical Specifications, Wavelength Specific

<b>Attenuation, maximum</b>	0.35 dB/km @ 1,300 nm
<b>Standards Compliance</b>	IEC 60794-1   TIA-492CAAB (OS2)

## Environmental Specifications

<b>Operating Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>EN50575 CPR Cable EuroClass Fire Performance</b>	Eca
<b>Environmental Space</b>	Universal Low Smoke Zero Halogen (ULSZH)

## Packaging and Weights

<b>Cable weight</b>	33 kg/km   22.175 lb/kft
---------------------	--------------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

CS-8W-250-EMEA - LightScope ZWP® Singlemode Fiber  
250um

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable