


E#O® Coaxial/Microduct Hybrid Buried Cable



- E#O is a solution that enables service providers the ability to bridge HFC networks to FTTx. The E#O composite coaxial/fiber product line combines fiber, microducts, and coaxial cable preinstalled in conduit
- Serves businesses in a new commercial serving area
- Mitigates future cost of fiber installation
- Pre-installed in high density PE conduit for added physical protection
- One-step installation saves on construction cost
- Ideal for commercial data customers that also require video
- All products tested to industry standards
- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	North America
Product Type	Coaxial fiber cable-in-conduit
Product Brand	E#O®
Government Funding	Build America Buy America (BABA) compliant*

General Specifications

Cable Series	P3 625
---------------------	--------

Dimensions

Height	48.26 mm 1.9 in
Width	48.26 mm 1.9 in
Outer Jacket Thickness, nominal	3.835 mm 0.151 in

Material Specifications

Outer Jacket Material	High density polyethylene (HDPE)
------------------------------	----------------------------------

Mechanical Specifications

Minimum Bend Radius	508 mm 20 in
Pulling Tension, maximum	659.977 kg 1455 lb

Environmental Specifications

Environmental Space Buried

Packaging and Weights

Weight, gross 836.348 kg/km | 562 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

- 360000000 - ConQuest® Empty Conduit, 12.7 mm, black
- CX3499999 - ConQuest® Empty Conduit, 1 1/2 in, SDR 13.5, terracotta
- 150T135 EMPTY DUCT COEX

360000000



ConQuest® Empty Conduit, 12.7 mm, black

Product Classification

Product Type	Empty conduit
Product Brand	ConQuest®

General Specifications

Color	Black
Conduit Type	Non-toneable
Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm ³ 0.035 lb/in ³
Density, minimum	0.941 g/cm ³ 0.034 lb/in ³
Design Standard	ASTM D3350-05
Wall Type	Smooth

Dimensions

Inner Diameter, nominal	10.008 mm 0.394 in
Outer Diameter, nominal	12.7 mm 0.5 in
Wall Thickness, minimum	1.346 mm 0.053 in
Nominal Size	12.7 mm

Material Specifications

Flexural Modulus, minimum	551.581 N/mm ² 80000 psi
Flexural Property Test Method	ASTM D790
Hydrostatic Design Basis	Not pressure rated
Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE)
Melt Flow Rate Test Method	ASTM D1238
Melt Flow Rate, maximum	0.39 g/10 min

360000000

Mechanical Specifications

Minimum Bend Radius, unsupported	152.4 mm 6 in
Tensile Property Test Method	ASTM D638
Tensile Strength at yield, minimum	20.684 N/mm ² 3000 psi
Pulling Tension, maximum	86.183 kg 190 lb

Environmental Specifications

Environmental Stress Crack Resistance	Failure rate of 10% within 96 hours
Environmental Stress Test Method	ASTM D1693, ESCR Condition B

Packaging and Weights

Weight, net	46.133 kg/km 31 lb/kft
--------------------	--------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance

CX3499999 | 150T135 EMPTY DUCT COEX



ConQuest® Empty Conduit, 1 1/2 in, SDR 13.5, terracotta

Product Classification

Product Type	Empty conduit
Product Brand	ConQuest®

General Specifications

Color	Terracotta
Conduit Type	Non-toneable
Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm ³ 0.035 lb/in ³
Density, minimum	0.941 g/cm ³ 0.034 lb/in ³
Design Standard	ASTM D3350-05
Wall Type	Smooth

Dimensions

Length	914.4 m 3000 ft
Inner Diameter, nominal	40.589 mm 1.598 in
Outer Diameter, nominal	48.26 mm 1.9 in
Wall Thickness Designation	SDR 13.5
Wall Thickness, minimum	3.581 mm 0.141 in
Nominal Size	1-1/2 in

Material Specifications

Flexural Modulus, minimum	551.581 N/mm ² 80000 psi
Flexural Property Test Method	ASTM D790
Hydrostatic Design Basis	Not pressure rated
Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE)
Melt Flow Rate Test Method	ASTM D1238

CX3499999 | 150T135 EMPTY DUCT COEX

Melt Flow Rate, maximum 0.39 g/10 min

Mechanical Specifications

Minimum Bend Radius, unsupported 508 mm | 20 in

Tensile Property Test Method ASTM D638

Tensile Strength at yield, minimum 20.684 N/mm² | 3000 psi

Pulling Tension, maximum 659.977 kg | 1455 lb

Environmental Specifications

Environmental Stress Crack Resistance Failure rate of 10% within 96 hours

Environmental Stress Test Method ASTM D1693, ESCR Condition B

Packaging and Weights

Weight, net 511.928 kg/km | 344 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance