

1-1427439-4



Indoor/Outdoor Fiber Optic Cable, 12-fiber, singlemode, OS2, LSZH, loose tube, gel-filled, 1000 m

OBSOLETE

This product was discontinued on: October 30, 2022

Replaced By:

760249711 Fiber indoor/outdoor cable, Gel-filled Central Tube, 12 fiber, Singlemode G.652.D and G.657.A1,
C-012-CN-8Z-M12BK/28G/093 Meters jacket marking, Black jacket color

Product Classification

Regional Availability	Asia
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	C-LN

General Specifications

Cable Type	Loose tube
Subunit Type	Gel-filled
Jacket Color	Black
Jacket Marking	Meters
Fibers per Subunit, quantity	12
Total Fiber Count	12

Dimensions

Cable Length	1000 m 3,280.84 ft
Diameter Over Jacket	8 mm 0.315 in

Mechanical Specifications

Minimum Bend Radius, loaded	160 mm 6.299 in
Minimum Bend Radius, unloaded	80 mm 3.15 in
Tensile Load, long term, maximum	800 N 179.847 lbf

1-1427439-4

Tensile Load, short term, maximum 1800 N | 404.656 lbf

Optical Specifications

Fiber Type OS2

Optical Specifications, Wavelength Specific

Standards Compliance TIA-492CAAB (OS2)

Environmental Specifications

Installation temperature -10 °C to +60 °C (+14 °F to +140 °F)

Operating Temperature -20 °C to +70 °C (-4 °F to +158 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Cable weight 73 kg/km | 49.054 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable