

HELIAX® LazrSPEED® Hybrid Cable, UL Type TC-OF-ER

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Hybrid cable, copper and fiber
Product Brand	HELIAX® LazrSPEED®

General Specifications

Application	Remote radio head
Cable Type	Wireless feeder
Conductors, quantity	12
Construction Type	Shielded
Fiber Short Description	RFF – 6AWG
Fiber Type, quantity	24
Fibers per Subunit, quantity	12
Inner Shield (Tape) Material	Corrugated aluminum
Jacket Color	Black
Outer Shield (Tape) Material	PVC
Strength Members	Glass reinforced plastic rod
Subunit, quantity	2
Total Fiber Count	24
Water Blocking Method	Water blocking tape(s) Water blocking threads

Dimensions

Buffer Tube/Subunit Diameter	0.24 in 6.096 mm
-------------------------------------	--------------------

760202911 | HTC-24MM-1206-APV

Diameter Over Jacket 1.42 in | 36.068 mm


Conductor Gauge 6 AWG

Electrical Specifications

dc Resistance Note Maximum value based on a standard condition of 20 °C (68 °F)

dc Resistance, maximum 0.412 ohms/kft | 1.352 ohms/km

Representative Image



Material Specifications

Ripcord Material Para-aramid synthetic fiber

Mechanical Specifications

Minimum Bend Radius, multiple bends, loaded 28.4 in | 721.36 mm

Minimum Bend Radius, multiple bends, unloaded 14.2 in | 360.68 mm

Minimum Bend Radius, single bend, unloaded 9.9 in | 251.46 mm

Tensile Load, long term, maximum 450 lbf | 2,001.699 N

Tensile Load, short term, maximum 1500 lbf | 6,672.33 N

Compression 250 lb/in | 4.465 kg/mm

Compression Test Method FOTP-41

Flex Test Method FOTP-104

Impact 4.34 ft lb | 5.884 N-m

Impact Test Method FOTP-25

Twist 10 cycles

Twist Test Method FOTP-85

760202911 | HTC-24MM-1206-APV

Optical Specifications

Fiber Type OM2+, LazrSPEED® 150 | OM2+, LazrSPEED® 150

Environmental Specifications

Installation temperature -30 °C to +70 °C (-22 °F to +158 °F)

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)

Storage Temperature -40 °C to +80 °C (-40 °F to +176 °F)

Cable Qualification Standards ANSI/ICEA S-104-696 | ANSI/ICEA S-87-640 | Telcordia GR-20 | Telcordia GR-409 | UL 1277

Environmental Space Wireless installation

Packaging and Weights

Cable weight 1590 lb/kft | 2,366.181 kg/km

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



Included Products

CS-5M-MP – LazrSPEED® 150 OM2+ Bend-Insensitive Multimode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable