


CX3450015 | 150B135P3875JCASS COEX

ConQuest® Cable in Conduit, 1 1/2 in, SDR 13.5, black (P3® 875 JCASS)



- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or are the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

OBSOLETE

This product was discontinued on: **March 13, 2015**

Product Classification

Regional Availability	North America
Product Type	Coaxial cable-in-conduit
Product Brand	ConQuest®
Product Series	875 Series

General Specifications

Cable Type	875 Series
Cable-In-Conduit Type	P3® in duct
Color	Black
Conduit Type	Non-toneable
Wall Type	Smooth

Dimensions

Length	762 m 2500 ft
Wall Thickness Designation	SDR 13.5
Nominal Size	1-1/2 in

Packaging and Weights

Weight, net	901.827 kg/km 606 lb/kft
--------------------	----------------------------

CX3450015 | 150B135P3875JCASS COEX

Included Products

- 5309103 P3® 875 JCASS – 75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground
- 5309193 P3® 875 JCASS – 75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground

75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground



- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or are the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	North America
Product Type	Coaxial hardline cable
Product Brand	P3®
Government Funding	Build America Buy America (BABA) compliant
Warranty	One year

General Specifications

Cable Type	875 Series
Construction Type	Swaged
Jacket Color	Black
Short Description	P3 875 JCASS SM PR997

Dimensions

Cable Length	762 m 2500 ft
Diameter Over Center Conductor, nominal	4.928 mm 0.194 in
Diameter Over Dielectric, nominal	20.244 mm 0.797 in
Diameter Over Jacket, nominal	24.257 mm 0.955 in
Diameter Over Outer Conductor, nominal	22.225 mm 0.875 in
Jacket Thickness, nominal	0.889 mm 0.035 in
Outer Conductor Thickness, nominal	0.991 mm 0.039 in

Electrical Specifications

Capacitance	50.197 pF/m 15.3 pF/ft
Capacitance Tolerance	±1.0 pF/ft

Characteristic Impedance	75 ohm
Characteristic Impedance Tolerance	±2 ohm
dc Resistance Note	Nominal values based on a standard condition of 20 °C (68 °F)
dc Resistance, Inner Conductor, nominal	1.378 ohms/km 0.42 ohms/kft
dc Resistance, Loop, nominal	1.804 ohms/km 0.55 ohms/kft
dc Resistance, Outer Conductor, nominal	0.427 ohms/km 0.13 ohms/kft
Jacket Spark Test Voltage	5000 Vac
Nominal Velocity of Propagation (NVP)	87 %
Operating Frequency Band	5–3000 MHz
Structural Return Loss	24 dB @ 1003–1218 MHz 24 dB @ 1219–1794 MHz 30 dB @ 5–1002 MHz
Structural Return Loss, Grade N	≥24 dB @ 1003–1218 MHz ≥24 dB @ 1219–1794 MHz ≥30 dB @ 5–1002 MHz

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.3	0.09
55.0	1.08	0.33
85.0	1.31	0.4
204.0	2.07	0.63
211.0	2.17	0.66
250.0	2.36	0.72
300.0	2.56	0.78
350.0	2.76	0.84
400.0	2.99	0.91
450.0	3.18	0.97
500.0	3.38	1.03
550.0	3.54	1.08
600.0	3.74	1.14
750.0	4.23	1.29
865.0	4.63	1.41
1002.0	5.02	1.53
1218.0	5.57	1.7
1500.0	6.39	1.95
1794.0	7.13	2.17

5309103 | P3® 875 JCASS

1800.0	7.14	2.18
2000.0	7.62	2.32
2200.0	8.09	2.46
2500.0	8.76	2.67
2700.0	9.19	2.8
3000.0	9.83	3

Material Specifications

Center Conductor Material	Copper-clad aluminum
Dielectric Material	Foam PE
Jacket Material	PE
Outer Conductor Material	Aluminum

Mechanical Specifications

Minimum Bend Radius, bonded	177.8 mm 7 in
Pulling Tension, maximum	396.893 kg 875 lb

Environmental Specifications

Corrosion Protection	Migraheal®
Environmental Space	Buried

Packaging and Weights

Packaging Type	Reel
Weight, gross	505.976 kg/km 340 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



75 Ohm P3® Trunk and Distribution Cable, black PE jacket, flooded for underground



Product Classification

Product Type	Coaxial hardline cable
Product Brand	P3®
Warranty	One year

General Specifications

Cable Type	875 Series
Construction Type	Swaged
Jacket Color	Black
Short Description	P3 875 JCASS SM PR997

Dimensions

Cable Length	762 m 2500 ft
Diameter Over Center Conductor, nominal	4.928 mm 0.194 in
Diameter Over Dielectric, nominal	20.244 mm 0.797 in
Diameter Over Jacket, nominal	24.257 mm 0.955 in
Diameter Over Outer Conductor, nominal	22.225 mm 0.875 in
Jacket Thickness, nominal	0.889 mm 0.035 in
Outer Conductor Thickness, nominal	0.991 mm 0.039 in

Electrical Specifications

Capacitance	50.197 pF/m 15.3 pF/ft
Capacitance Tolerance	±1.0 pF/ft
Characteristic Impedance	75 ohm
Characteristic Impedance Tolerance	±2 ohm

dc Resistance Note	Nominal values based on a standard condition of 20 °C (68 °F)
dc Resistance, Inner Conductor, nominal	1.378 ohms/km 0.42 ohms/kft
dc Resistance, Loop, nominal	1.804 ohms/km 0.55 ohms/kft
dc Resistance, Outer Conductor, nominal	0.427 ohms/km 0.13 ohms/kft
Jacket Spark Test Voltage	5000 Vac
Nominal Velocity of Propagation (NVP)	87 %
Operating Frequency Band	5–3000 MHz
Structural Return Loss	24 dB @ 1003–1218 MHz 24 dB @ 1219–1794 MHz 30 dB @ 5–1002 MHz
Structural Return Loss, Grade N	≥24 dB @ 1003–1218 MHz ≥24 dB @ 1219–1794 MHz ≥30 dB @ 5–1002 MHz

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	0.3	0.09
55.0	1.08	0.33
85.0	1.31	0.4
204.0	2.07	0.63
211.0	2.17	0.66
250.0	2.36	0.72
300.0	2.56	0.78
350.0	2.76	0.84
400.0	2.99	0.91
450.0	3.18	0.97
500.0	3.38	1.03
550.0	3.54	1.08
600.0	3.74	1.14
750.0	4.23	1.29
865.0	4.63	1.41
1002.0	5.02	1.53
1218.0	5.57	1.7
1500.0	6.39	1.95
1794.0	7.13	2.17
1800.0	7.14	2.18
2000.0	7.62	2.32

5309193 | P3® 875 JCLASS

2200.0	8.09	2.46
2500.0	8.76	2.67
2700.0	9.19	2.8
3000.0	9.83	3

Material Specifications

Center Conductor Material	Copper-clad aluminum
Dielectric Material	Foam PE
Jacket Material	PE
Outer Conductor Material	Aluminum

Mechanical Specifications

Minimum Bend Radius, bonded	177.8 mm 7 in
Pulling Tension, maximum	396.893 kg 875 lb

Environmental Specifications

Corrosion Protection	Migraheal®
Environmental Space	Buried

Packaging and Weights

Packaging Type	Reel
Weight, gross	505.976 kg/km 340 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

