



E20® Coaxial/Fiber Hybrid Indoor Cable

- E#0 is a solution that enables service providers the ability to bridge HFC networks to FTTx. The E#0 composite coaxial/fiber product line combines fiber, microducts, and coaxial cable under one jacket
- Serves businesses in a new commercial serving area
- Mitigates future cost of fiber installation
- Saves on initial installation due to “single sheath” vs. multiple sheaths
- Ideal for commercial data customers that also require video
- All products tested to industry standards

Product Classification

Product Type	Hybrid cable, coax and fiber
Product Brand	E#0®
Product Series	6 Series
Warranty	One year

General Specifications

Cable Series	Series 6
Total Fiber Count	2

Dimensions

Height	11.887 mm 0.468 in
Outer Jacket Thickness, nominal	0.508 mm 0.02 in

Mechanical Specifications

Minimum Bend Radius	81.28 mm 3.2 in
Pulling Tension, maximum	33.112 kg 73 lb

Environmental Specifications

Environmental Space	Riser
----------------------------	-------

Packaging and Weights

Weight, gross	89.29 kg/km 60 lb/kft
----------------------	-------------------------

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

Included Products

- 760150490
Z-002-DS-8W-FSUBK/D - Fiber indoor/outdoor cable, TeraSPEED® LSZH Riser Distribution, 2 fiber single-unit, Singlemode G.652.D and G.657.A1, Feet jacket marking, Black jacket color, Dca flame rating
- 7702003
F677TSVR XP - XPRESSPREP® Coaxial Drop Cable, 75 Ohm, Series 6, black flame retardant PVC jacket

* Footnotes

Warranty

For more information, please consult our Product Warranty guidelines