## PFC-S12012



Powered Fiber Cable, OS2, 12 Fibers, Outdoor, 12AWG Conductor, meter, feet

- Easy peel, stranded conductors for maximum cable flexibility and rapid access
- Polarization indentation along one side of the cable for polarity identification
- No special tools or mounting hardware required usage of a standard "FTTH" pressure clamp for aerial installation
- Easy split of cable into three separate sections for separate routing in closures, as needed for installation
- Polyethylene jacket for outdoor duct or direct buried applications

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Hybrid cable, fiber and power

**Ordering Note**Minimum order quanity is 500 meter

## General Specifications

Cable Type Stranded outdoor

Fiber Short Description PFC-012

Jacket Color Black

Total Fiber Count 12

#### **Dimensions**

 Height Over Jacket
 4.318 mm | 0.17 in


 Width Over Jacket
 11.43 mm | 0.45 in

Conductor Gauge 12 AWG

## Outline Drawing



# PFC-S12012



#### Mechanical Specifications

Minimum Bend Radius, loaded50.8 mm | 2 inMinimum Bend Radius, unloaded30.48 mm | 1.2 inTensile Load, long term, maximum133.447 N | 30 lbfTensile Load, short term, maximum440.374 N | 99 lbfVertical Rise, maximum122.011 m | 400.3 ft

**Optical Specifications** 

**Fiber Type** G.657.A2, TeraSPEED® | OS2

## **Environmental Specifications**

Installation temperature

-10 °C to +60 °C (+14 °F to +140 °F)

Operating Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Cable Qualification Standards

Telcordia GR-20-CORE Issue 4

Environmental Space Outdoor

Jacket UV Resistance UV stabilized

Packaging and Weights

**Cable weight** 109.975 kg/km | 73.9 lb/kft

**COMMSCOPE®** 

# PFC-S12012

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### Included Products

CS-8G-PFC – Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T

G.657.A2, B2)

