



Wall Mount Building Enclosure configured for two G2 Modular Cassettes

## OBSOLETE

This product was discontinued on: **March 31, 2021**

### Replaced By:

760248901      Wall Mount Building Enclosure configured for two G2 Style modules, splice cassettes or adapter packs  
WB2-EMT-BK-2P-MOD

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber wall box  |
| <b>Product Series</b>        | WBE   |

## General Specifications

|                    |   |
|--------------------|---|
| <b>Application</b> | Accepts one RoloSplice   Accepts two G2 modular cassettes |
| <b>Color</b>       | Black   |
| <b>Interface</b>   | Unloaded  |

## Dimensions

|               |                  |
|---------------|------------------|
| <b>Height</b> | 279.4 mm   11 in |
| <b>Width</b>  | 330.2 mm   13 in |
| <b>Depth</b>  | 63.5 mm   2.5 in |

## Material Specifications

|                      |       |
|----------------------|-------|
| <b>Material Type</b> | Steel |
|----------------------|-------|

## Environmental Specifications

|                            |        |
|----------------------------|--------|
| <b>Environmental Space</b> | Indoor |
|----------------------------|--------|

# 760164616 | WBE-EMT-BK-2P-MOD

---

**Safety Standard** UL

## Packaging and Weights

**Weight, net** 2.72 kg | 5.997 lb

## Regulatory Compliance/Certifications

### Agency

### Classification

|               |  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

