



## Rapid Fiber™ EFDT NID Wall Mounting Fiber Box, outdoor, 12 SC /APC, 8-way splitter

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections
- Weatherproof housing suitable for external environmental conditions

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Fiber wall box
<b>Product Brand</b>	Rapid Fiber™
<b>Product Series</b>	EFDT

## General Specifications

<b>Functionality</b>	Patching   Splitting
<b>Access</b>	Front
<b>Distribution Type</b>	1 x 8 splitter
<b>Enclosure Color</b>	Gray
<b>Front Cover Type</b>	Hinged with lock
<b>Interface, Input</b>	SC
<b>Interface Feature, Input</b>	APC
<b>Mounting</b>	Wall
<b>Port, quantity</b>	12
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1

## Dimensions

<b>Height</b>	264.16 mm   10.4 in
<b>Width</b>	179.07 mm   7.05 in
<b>Depth</b>	71.12 mm   2.8 in

## Material Specifications

# 760235625 | EFDT-NID-1181528

---

**Enclosure Material Type** LSZH thermoplastic

## Optical Specifications

**Fiber Mode** Singlemode

**Fiber Type** G.657.A2

**Wavelength Range** 1260–1650 nm

**Insertion Loss, Splitter, maximum** 11 dB

**Return Loss, Connector, minimum** 55 dB

## Environmental Specifications

**Environmental Space** Outdoor

**Qualification Standards** IEC 60529, IP55 | IEC 61753-1, category G

## Packaging and Weights

**Packaging quantity** 8

**Packaging Type** Box | Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

