

FDT-AL212NXB0000



iFDT Indoor Fiber Distribution Terminal, 12-fiber, LC/APC, soft-wall pigtailed, heat shrink splice trays

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

Product Classification

Regional Availability	North America
Product Type	Fiber distribution terminal
Product Series	IFDT

General Specifications


Adapters, quantity	6
Cable Entry Location	Bottom right Top right
Cable Type	Pigtails - Stranded
Color	Putty white
Front Door Type	Double hinged
Growth Configuration	Fully loaded
Interface	LC/APC
Lock Type	Padlock ready
Mounting	Wall
Port, quantity	12
Splice Tray Chip Type	Heat shrink
Splicing Capacity, maximum	12

Dimensions

Height	184.15 mm 7.25 in
Width	299.72 mm 11.8 in
Depth	82.55 mm 3.25 in

Ordering Tree

FDT-AL212NXB0000



Material Specifications

Finish Powder coated
Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor
Qualification Standards NEMA, Type 12 | Telcordia GR-2898-CORE

Packaging and Weights

Packaging quantity 1

FDT-AL212NXB0000

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

