

RJ45 Patch Panel, Q Series, category 6A, 24-port, black, ,STP, loaded



OBSOLETE

This product was discontinued on: October 1, 2018

Product Classification

Regional Availability	Asia EMEA Latin America North America
Portfolio	NETCONNECT®
Product Type	RJ45 patch panel

General Specifications

ANSI/TIA Category	6A
Cable Type	Shielded
Color	Black
Growth Configuration	Fully loaded
Interface, front	RJ45 jack
Panel Mounting	Flush
Panel Style	Straight
Rack Type	EIA 19 in
Rack Units	1
Termination Type	IDC
Total Ports, quantity	24
Transmission Standards	ANSI/TIA-568-C.2 ISO/IEC 11801 Class EA
Wiring	T568A T568B

Dimensions

Height	44.45 mm 1.75 in
---------------	--------------------

1-1671607-2

Width 482.6 mm | 19 in

Material Specifications

Material Type High-impact, flame retardant, thermoplastic | Steel

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Box

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



Included Products

1-1671660-1 – RJ45 Modular Jack Q-Series, category 6A, shielded, 8-position



RJ45 Modular Jack Q-Series, category 6A, shielded, 8-position

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	NETCONNECT®
Product Type	Modular jack
Product Series	Q Series

General Specifications

ANSI/TIA Category	6A
Cable Type	Shielded
Color	Black
Conductor Type	Solid Stranded
Outlet Type	Standard
Termination Type	IDC
Transmission Standards	ANSI/TIA-568-C.2 ISO/IEC 11801 Class EA
Wiring	T568A T568B

Dimensions

Contact Plating Thickness	1.27 µm
Panel Thickness, recommended	1.6 mm 0.063 in

Material Specifications

Contact Base Material	Beryllium copper
Contact Plating Material	Gold
Material Type	Polycarbonate

1-1671660-1

Environmental Specifications

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging quantity 12

Packaging Type Tray in box

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

