

760116996 | RFE-HDM-096-8W-LC02-KRD

ReadyPATCH® Singlemode Keyed High Density Module, 96 LC ports, red

OBSOLETE

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	ReadyPATCH® TeraSPEED®

General Specifications

Functionality	Breakout
Adapters, quantity, front	48
Adapters, quantity, rear	8
Color, front	Red
Color, rear	Gray
Interface, front	LC/UPC
Interface Feature, front	Keyed
Interface, rear	MPO
Interface Feature, rear	Male
Shuttered	Yes
Total Fibers, quantity	96
Total Ports, quantity, front	96

Dimensions

Height	32.51 mm 1.28 in
Width	424.18 mm 16.7 in
Depth	114.3 mm 4.5 in

Optical Specifications

Fiber Type	G.652.D and G.657.A1, TeraSPEED® OS2
Insertion Loss Change, mating	0.3 dB

760116996 | RFE-HDM-096-8W-LC02-KRD

Insertion Loss Change, temperature	0.3 dB
Insertion Loss, maximum	1.15 dB

Environmental Specifications

Safety Standard	UL
------------------------	----

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)