

NG4-VDML2MDA200C1K



NG4access® Module VAM, DWDM, 8 channels, upgrade port, EXP port, 100 GHz channel spacing, starting channel 20, 2 circuits, Mux, LC/APC, left, 1 test port

- VAMs help enhance optical transport systems by providing flexible, easy to incorporate optical components into the network
- VAMs increase fiber capacity and help troubleshooting or distributing signals to multiple subscribers
- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	DWDM module
Product Brand	NG4access®
Product Series	FACT NG4
Government Funding	Build America Buy America (BABA) compliant*

General Specifications

Device Type	Plug-and-play module
Functionality	Multiplexing
Application	For use with NG4 access frames
Circuits, quantity	2
Distribution Type	8-channel DWDM
Interface, front	LC/APC
Interface, Input	LC/APC
Interface, Output	LC/APC
Multiplexers, quantity	2
Port Type, optional	Express port Test port Upgrade port
Tray Orientation	Left orientation

NG4-VDML2MDA200C1K

Dimensions

Height	13.21 mm 0.52 in
Width	159.77 mm 6.29 in
Depth	130.3 mm 5.13 in

Optical Specifications

Channel Spacing	100 GHz
Starting Channel Number	20

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

