# RCP-C3ZAPUZ06100



RapidFiber® Termination Panel, 144-Position 3RU, singlemode, LC/APC to LC/APC, 61 m

#### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber patch panel, with rapid cable

Product Brand RapidFiber®

Product Series RCP

#### General Specifications

**Functionality** Patching

Body Style Symmetrical

Cable Exit Location Rear, left side

Cable Stub TypeIndoor, microcable

**Color** Putty white

Door Type, front Hinged | Slide latch | Transparant

Growth ConfigurationFully loadedInterface, frontLC/APCInterface, rearLC/APC

Patch Cord Entry Location Front, left side | Front, right side

Rack Type EIA 19 in | EIA 23 in

Rack Units 3

Shelf Movement Sliding

Total Fibers, quantity 144

Total Ports, quantity 144

**Transmission Standards** IEC 60794-2 | ISO/IEC 11801 | TIA/EIA-568-B.3

**Dimensions** 

 Height
 133.35 mm | 5.25 in


 Width
 482.6 mm | 19 in

COMMSCSPE®

# RCP-C3ZAPUZ06100

**Depth** 381 mm | 15 in **Cable Length** 61 m | 200.131 ft

### Ordering Tree



### Material Specifications

**Finish** Powder coated

Material Type Steel

**Optical Specifications** 

Fiber Mode Singlemode

**Fiber Type** G.652.D | G.657.A2/B2

COMMSC PE°

# RCP-C3ZAPUZ06100

## **Environmental Specifications**

Operating Temperature  $-5 \,^{\circ}\text{C}$  to  $+55 \,^{\circ}\text{C}$  (+23  $^{\circ}\text{F}$  to +131  $^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

**Relative Humidity** 5%–85%, non-condensing

Qualification Standards NEBS Level 3 | Telcordia GR-1435 | Telcordia GR-326 | Telcordia GR-409 | UL 1863

#### Packaging and Weights

Packaging quantity 1

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

