



Vertical Power Distribution Strip, 125V, 15A, Surge Protected, with Circuit Breaker, Twistlock plug

OBSOLETE

This product was discontinued on: December 31, 2014

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Vertical power strip
Ordering Note	Not available in Mexico

General Specifications

Color	Black
On/Off Switch	No
Plug Standard	NEMA L5-15P, twistlock
Receptacle Standard	NEMA 5-15R
Receptacle, quantity	20

Dimensions

Height	41 mm 1.614 in
Width	1683 mm 66.26 in
Depth	41 mm 1.614 in
Cable Length	3 m 9.843 ft

Electrical Specifications

Circuit Breaker	Yes
Current	15 A
Overcurrent Protection	15 A
Power Frequency	50/60 Hz

760083618 | PSV5-15SP-CBTP

Power Rating, maximum	1.4 kW
Surge Indicator	Yes
Surge Protection	Yes
Voltage	125 V

Material Specifications

Finish	Powder-coated, textured
Material Type	Steel

Environmental Specifications

Safety Standard	UL cUL
------------------------	----------

Packaging and Weights

Included	Instruction sheet Plastic bottom mounting clip Two #10-32 x 1/2 in panhead screws Two plastic top mounting clips Vertical PDU
Packaging quantity	1
Weight, net	5 kg 11.023 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

