



SYSTIMAX 360™ PATCHMAX® Panel Kit, 2U, 48 port

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	SYSTIMAX®
Product Type	RJ45 patch panel
Product Brand	GigaSPEED X10D®

General Specifications

Cable Type	Unshielded
Color	Cool gray   Satin chrome
Intelligence Type	iPatch® ready
Panel Style	Straight
Rack Type	EIA 19 in
Rack Units	2
Total Ports, quantity	48

Dimensions

Height	88.9 mm   3.5 in
Width	482.6 mm   19 in
Depth, with cable management	266.7 mm   10.5 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic   Powder-coated steel
---------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing

Flammability Rating	UL 94 V-0
Safety Standard	UL   cUL

Packaging and Weights

Packaging quantity	1
--------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

