760152595 | 360-IPR-1100-E-GS6-2U-48



SYSTIMAX 360™ GigaSPEED X10D® 1100GS6 Evolve Category 6A U /UTP Patch Panel, 48 port

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

Portfolio SYSTIMAX®

Product Type RJ45 patch panel

Product Brand GigaSPEED X10D® | SYSTIMAX 360™

Product Series UTG

General Specifications

ANSI/TIA Category 6A

Cable Type Unshielded

Color Cool gray | Satin chrome

Conductor Type Solid | Stranded

Intelligence Type iPatch® ready

Modules, quantity

Panel StyleStraightRack TypeEIA 19 in

Rack Units 2

Termination Type IDC

Total Ports, quantity 48

Transmission StandardsANSI/TIA-568.2-D | ISO/IEC 11801 Class EA

Wiring T568A | T568B

Dimensions

 Height
 88.9 mm | 3.5 in

 Width
 482.6 mm | 19 in

 Depth, with cable management
 165.1 mm | 6.5 in

Page 1 of 3



760152595 | 360-IPR-1100-E-GS6-2U-48

Compatible Diameter Over Dielectric, maximum1.168 mm | 0.046 inCompatible Diameter Over Dielectric, minimum0.762 mm | 0.03 in

Compatible Conductor Gauge, solid 22-24 AWG | 21 AWG (for CommScope GigaREACH cable

only)

Compatible Conductor Gauge, stranded 22-24 AWG

Electrical Specifications

Current Rating at Temperature 1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface1,500 Vac @ 60 HzDielectric Withstand Voltage, RMS, contact-to-contact1,000 Vac @ 60 Hz

Insulation Resistance, minimum 500 MOhm

Remote Powering Fully complies with the recommendations set forth by IEEE

802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN

50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

Material Specifications

Contact Plating Material Precious metals

Material Type High-impact, flame retardant, thermoplastic | Powder-

coated steel

Termination Contact Plating Nickel

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Plug Insertion Life, test plug IEC 60603-7 compliant plug

Plug Retention Force, minimum 133 N | 29.9 lbf

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Relative Humidity Up to 95%, non-condensing

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging Material Eco-friendly, single-use plastics-free

Packaging quantity 1

COMMSCOPE®

760152595 | 360-IPR-1100-E-GS6-2U-48

Weight, net 1.814 kg | 4 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

