

CV6317-000 | TENIO-B6-NT-0-V



TENIO™ Small Fiber Optic Splice Closure, Gel Cable sealing, no pre-installed trays, with test valve

- Single-ended, toolless closure for splicing feeder, access and drop cables
- Features modular building blocks that fastens installation and reduces inventory
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- Compatible with CommScope's CWDM modules and optical splitter trays

Product Classification

Regional Availability	EMEA Latin America
Product Type	Single-ended, rectangular fiber closure
Product Brand	TENIO™
Product Series	TENIO

General Specifications

Cable Entry Drop Port Style	Gel block
Cable Entry Main Port Style	Gel block
Cable Ports Quantity, total	6 multi-out ports (30 cables)
Cable Sealing Type	Compressed gel
Closure Sealing Type	Side latch
Closure Style	Single-ended
Color	Black
Mounting	Wall
Network Area Type	Distribution Drop
Splice Tray Included, quantity	0
Splices per Tray, quantity	12
Splicing Capacity, Single Fusion, maximum	144
Splicing Type, Supported	Single fusion

Dimensions


Height	230 mm 9.055 in
Width	134 mm 5.276 in
Length	389 mm 15.315 in

CV6317-000 | TENIO-B6-NT-0-V

Main Cable Diameter, maximum

16 mm | 0.63 in

Ordering Tree



Material Specifications

Material Type

Impact-resistant polymer

Environmental Specifications

Environmental Space

Below ground | Buried

Qualification Standards

IEC 61300, 2 m waterhead

Water Resistance

Flash test valve at 5 psi (40 kPa)

Packaging and Weights

Packaging quantity

1

Packaging Type

Box | Carton

Weight, net

1 kg | 2.205 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

