

VI-48-23-TT-DES-BK



Standard BNC Bulkhead Panel, 2 RU, 2 x 24, black

OBSOLETE

Product Classification

Regional Availability	North America
Product Type	Video patch panel

General Specifications

Application	For use with BNC HD standard video patch cords
Color	Black
Growth Configuration	Fully loaded
Interface, front	BNC female adapter
Interface, rear	BNC female adapter
Mounting	Rack, horizontally oriented
Rack Type	EIA 23 in
Rack Units	2
Total Ports, quantity	48

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in

Electrical Specifications

Characteristic Impedance	75 ohm
---------------------------------	--------

Material Specifications

Finish	Powder coated
Material Type	Steel

VI-48-23-TT-DES-BK

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Storage Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

