

CC2258-000 | FOMS-FPS-O-SIL1-48

FOMS-FPS Fiber Termination/Splice Panel, 48 LC/UPC, singlemode, 1RU, 19 in, gray

Product Classification

| | |
|------------------------------|--------------------------|
| Regional Availability | EMEA |
| Portfolio | CommScope® |
| Product Type | Fiber patch/splice panel |
| Product Series | FOMS-FPS |

General Specifications

| | |
|------------------------------|-------------------------------------|
| Functionality | Patching Splicing |
| Color | Gray |
| Color, front | Gray |
| Interface, front | LC/UPC |
| Rack Type | EIA 19 in EIA 23 in ETSI 600 mm |
| Rack Units | 1 |
| Shelf Movement | Hinged |
| Total Ports, quantity | 48 |

Dimensions

| | |
|---------------|--------------------|
| Height | 44.45 mm 1.75 in |
| Width | 482.6 mm 19 in |

Ordering Tree

CC2258-000 | FOMS-FPS-O-SIL1-48

FOMS-FPS - X - X X XX - XX

| | | | | | | | | | | | | | | | | | | | |
|------------------------------------|---|------------------|--|--|----------------------|---------------------------|--|----------------------------|--|-----|-----|-------|-----|-----|----|-----|--|----|--|
| Chassis type | | | | Number of pigtails and/or connector ports | | | | | | | | | | | | | | | |
| <input type="radio"/> | 19" - 44 mm high | | | 48 | (for LC and MU only) | | | | | | | | | | | | | | |
| Shelf type | | | | 24 | | | | | | | | | | | | | | | |
| <input type="radio"/> | Patching only (jumpers, breakout cable) | | | 16 | (not for LC and MU) | | | | | | | | | | | | | | |
| <input type="radio"/> | Splicing and patching (loose tube cable, ribbon, IFC) | | | 12 | (not for LC and MU) | | | | | | | | | | | | | | |
| | | | | 0 | | | | | | | | | | | | | | | |
| Tray type/pigtails | | | | Connector adapter with retainer | | | | | | | | | | | | | | | |
| Secondary coated pigtails included | | Splice protector | | Jumpers leave shelf | | NN No connectors/pigtails | | | | | | | | | | | | | |
| | | | | Right front | | Left front | | Min.return loss | | SC | FC | E2000 | LC | DIN | ST | MU | | | |
| Not applicable (patching only) | | | | N | | M | | Single Mode Standard | | | | | | | | | | | |
| No | | SMOUV* | | E | | G | | 45 dB (PC) | | | | | | DO | | TO | | | |
| No | | ANT* | | F | | H | | 50 dB (UPC) | | S1 | F1 | | | | | | | U1 | |
| Yes | | SMOUV* | | I | | K | | 60 dB (APC 8°) | | S2 | F2 | E9 | L2 | | | | | | |
| Yes | | ANT* | | J | | L | | 60 dB (APC 9°) | | S3 | | | | | | | | | |
| | | | | | | | | Single Mode Low Loss | | | | | | | | | | | |
| | | | | | | | | 50 dB (UPC) | | S6 | | | | | | | | | |
| | | | | | | | | 60 dB (APC 8°) | | S7 | E8 | | | | | | | | |
| | | | | | | | | 60 dB (APC 9°) | | S8 | | | | | | | | | |
| | | | | | | | | Single Mode Consumer Grade | | | | | | | | | | | |
| | | | | | | | | 50 dB (UPC) | | SC | FC | LC | | | | | | | |
| | | | | | | | | 60 dB (APC 8°) | | SD | FD | LD | | | | | | | |
| | | | | | | | | Multi Mode | | | | | | | | | | | |
| | | | | | | | | 50/900 μ | | S5D | F5D | E5D | L5D | | | T5D | | | |
| | | | | | | | | 62.5/900 μ** | | S5E | F5E | E5E | L5E | | | T5E | | | |

* Splice protectors not included in the kit
 ** In case of adapters only (no pigtails included) use S5D, F5D, E5D, L5D and T5D.

Material Specifications

Material Type Ethylene-propylene (EP) | Polyethylene terephthalate (PET)

Optical Specifications

Fiber Mode Singlemode

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

