

EPX 1U sliding drawer panel, accepts (4) G2 modules or adapter packs providing up to 48 duplex LC or 32 MPO ports



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	EPX

General Specifications

Application	Accepts four G2 modular cassettes
Color	Black
Intelligence Type	Not iPatch® ready
Interface, front	Unloaded
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Sliding
Total Ports, quantity	0

Dimensions

Height	43.85 mm 1.726 in
Width	482 mm 18.976 in
Depth	250 mm 9.843 in

Material Specifications

Finish	Powder coated
Material Type	Steel

Environmental Specifications

Safety Standard UL

Packaging and Weights

Packaging quantity 1

Weight, net 1.512 kg | 3.333 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

