860633531 | OCFPS1U-CYS311L2-SUB

OCFPS Fiber Optic CWDM Panel, double mux, 16 channels, 1311 nm starting wavelength, 20 nm channel spacing, LC/APC, 1U, 19 in, gray



Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	CWDM patch panel
Product Series	OCFPS

General Specifications

Device Type	Patch panel
Functionality	Multiplexing
Technology Type	Thin film filter (TFF)
Circuits, quantity	2
Distribution Type	16-channel CWDM
Interface, front	LC/APC
Multiplexers, quantity	2
Rack Units	1
Dimensions	
Height	/35mm 1713 in

Height	43.5 mm 1.713 in
Width	440 mm 17.323 in
Depth	210 mm 8.268 in

Ordering Tree

Page 1 of 2

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: July 14, 2022



860633531 | OCFPS1U-CYS311L2-SUB

OCFPS 1U - X X X X X X X X

Туре		
IHU 1	U High 19" wide	
plitter Gra	de	
and the second se	l type	
	nar grade P	1
umber of	nar grade (low Splitters	1055)
	Shelf	type 1
	Grade A	Grade P/O
1 x 2	16	-
2 x 2	16	-
1 x 4		6
2 x 4		6
1 x 8		6
2 x 8	17	6
1 x 16	4	2
2 x 16	-	2
1 x 32		2
2 x 32		1

Optical Specifications

Channel Spacing20 nmStarting Wavelength1311 nm

1

Packaging and Weights

Packaging quantity

Page 2 of 2

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: July 14, 2022

