

# FPX-AF-24APL06

---

FPX Fiber Optic Adapter Pack Only, Multimode, 24 fiber, LC/UPC adapter, left, beige, putty white

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber adapter pack
<b>Product Series</b>	FPX

## General Specifications

<b>Application</b>	For use with FPX panels
<b>Adapter Color</b>	Beige
<b>Adapters, quantity, front</b>	12
<b>Body Style</b>	Duplex   Left orientation
<b>Color, front</b>	Putty white
<b>Interface</b>	LC/UPC
<b>Total Ports, quantity, front</b>	24

## Dimensions

<b>Height</b>	33.02 mm   1.3 in
<b>Width</b>	176.53 mm   6.95 in

## Ordering Tree

# FPX-AF-24APL06

FPX - AF - X X A P X X X X X X

## Number of Fiber Ports per Bulkhead

12	12 Fibers <sup>1</sup>
24	24 Fibers <sup>2</sup>
00	None

## Pack Orientation

L	Left adapter pack
R	Right adapter pack

## Adapter Style

00	None
Singlemode	
07	SC/APC
0J	SC/APC
08	LC/APC
0Z	LC/APC
Multimode	
A6	LCMM - AQUA <sup>3</sup>
A9	SCMM - AQUA <sup>3</sup>

## Pigtail Length

LEAVE BLANK	Adapters only
3	3 meter pigtails

## Pigtail Type

LEAVE BLANK	Adapters only
R	Ribbon
P	Stranded

## Fiber Type

LEAVE BLANK	Adapters only
S	Singlemode
D	50/125 Multimode (OM3)
Q	50/125 Multimode (OM4)

<sup>1</sup> SC only

<sup>2</sup> LC only

<sup>3</sup> CommScope recommends the use of aqua adapters to identify OM3 and OM4 circuits

## Optical Specifications

**Fiber Mode** Multimode

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Storage Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Bag | Carton

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](https://www.commscope.com/ProductCompliance)

ROHS

Compliant

# FPX-AF-24APL06

---

UK-ROHS

Compliant

