579980-000 | FOSC-400D5-72-1-NNN



FOSC® 400 D5 Fiber Optic Splice Closure, Heat Shrink Cable sealing, one pre-installed 72-splice tray

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

Product Classification

Regional Availability	Asia EMEA
Product Type	Single-ended, round fiber closure
Product Brand	FOSC®
Product Series	FOSC 400
General Specifications	
Cable Blocking Components	None
Cable Entry Drop Port Style	Round
Cable Entry Main Port Style	Oval
Cable Ports Quantity, total	1 oval port (2 cables) + 5 round ports
Cable Sealing Type	Heat shrink
Closure Sealing Type	Dome-to-base clamp with O-ring
Closure Style	Single-ended
Color	Black
Flash Test Valve	None
Ground Feed-through	None
Mounting	Pole Strand Wall
Network Area Type	Feeder
Splice Tray Included, quantity	1
Splice Tray Type Included	72-way, heat shrink
Splicing Capacity, Mass Fusion, maximum	1152
Splicing Capacity, Single Fusion, maximum	576
Splicing Capacity, Single Splice, 12 fibers, maximum	576

Page 1 of 4

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 3, 2023



FOSC-400D5-72-1-NNN 579980-000 |

Splicing Capacity, Single Splice, 6 fibers, maximum	288
Splicing Type, Supported	Mass fusion
Dimensions	
Length	710 mm 27.953 ir
Diameter	240 mm 9.449 in
Diameter, with clamp	260 mm 10.236 ir
Main Cable Diameter, maximum	25 mm 0.984 in


- ---

. . .

Dimension Drawing

• • **~**·

000




Ordering Tree

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 3, 2023



579980-000 FOSC-400D5-72-1-NNN



V Pre-installed flash test valve No flash test valve Ground feedthrough © Pre-installed ground feedthrough N No ground feedthrough



Number of splice trays

	No trays	
	A4	
14/8	A8 H	
16	BH	
	D5/B №	
	D5 M	

A A closure can accept a mix of standard and slim trays; please contact your local sales representative

Maximum 8 trays in case of S6 or A6 tray type

B closure can initially be fitted with trays; however, retrofitting a standard "B" closure (delivered with 4 trays or fewer) with a 5th and 6th tray is not possible. The B closure can be ordered with up to 5 trays pre-installed and capacity for later addition of a 6th tray (FOSC-400B4303///6...) If 5 or 6 trays are required, a storage basket cannot be used.

^{1d} If 7 or 8 trays are required, a storage basket cannot be used.

Material Specifications

Material Type

Impact-resistant polymer

Environmental Specifications

Environmental Space	Below ground Buried
Qualification Standards	IEC 61300, 6 m waterhead
Packaging and Weights	
Packaging quantity	1
Packaging Type	Box Carton
Weight, net	6 kg 13.228 lb

Page 3 of 4

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 3, 2023



579980-000 | FOSC-400D5-72-1-NNN

Designed, manufactured and/or distributed under this quality management system

Regulatory Compliance/Certifications

Agency

Classification

Compliant/Exempted

Compliant/Exempted

CHINA-ROHS

ISO 9001:2015

ROHS



Above maximum concentration value

Page 4 of 4

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 3, 2023

