AFGLGSFL1

Base Product



Fiber Patch Cord, Singlemode G.657.A2, Grade B, LC/APC to SC/UPC, Simplex, 1.6 mm LSZH jacket

Product Classification

Asia Australia/New Zealand Europe Latin America Middle East /Africa North America
CommScope®
Fiber patch cord, simplex
AFG
1
Green
1
Blue
LC/APC
SC/UPC
1
IEC 61755
1 – 999
1 – 999
1.6 mm 0.063 in


Ordering Tree

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024



AFGLGSFL1



Mechanical Specifications

Minimum Bend Radius, loaded	50 mm 1.969 in
Minimum Bend Radius, unloaded	30 mm 1.181 in
Tensile Load, long term, maximum	33 N 7.419 lbf
Tensile Load, short term, maximum	110 N 24.729 lbf
Cable Crush Resistance, maximum	3.5 N/mm 19.986 lb/in
Mating Durability, maximum	0.2 dB @ 500 cycles

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2, TeraSPEED®
Performance Grade	IEC Random Mating Grade B
Insertion Loss, maximum, connector A	0.25 dB
Insertion Loss, maximum, connector B	0.25 dB
Return Loss, minimum, connector A	65 dB
Return Loss, minimum, connector B	50 dB

Environmental Specifications

20 °C to +60 °C (-4 °F to +140 °F)
oual Rated LSZH/Riser

Regulatory Compliance/Certifications

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024



AFGLGSFL1

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant



r, Singlemode G.657.A2, 1.6
de, Blue, Short Boot

* Footnotes

Performance Grade Guarantee to meet IEC 61755-1 Random Mating requirement

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 12, 2024

