

# CGSSD | IPO6-12PUTP-1LK12-1LK12

## Base Product



InstaPATCH® Cu GigaSPEED XL® U/UTP Plenum Preterminated Copper Cable, dual row OneLink 2x6 to dual row OneLink 2x6, 12 links

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

### Portfolio

CommScope®

### Product Type

Copper trunk cable assembly

### Product Brand

GigaSPEED XL® | InstaPATCH® Cu

## General Specifications

### ANSI/TIA Category

6

## Dimensions

### Cable Assembly Length Range (m)

2 – 100

### Cable Assembly Length Range (ft)

7 – 328

## Ordering Tree

C A A A C - 1 1 H A B B F 0 5 0

| Cable Type                            | Connector B                                | Orientation A           | Orientation B           |
|---------------------------------------|--|-------------------------|-------------------------|
| A Cat 6A X10D – U/UTP (Plenum)        | A Outlet* – Single Row Standard Density    | 1 Trident Series Flat   | 1 Trident Series Flat   |
| B Cat 6A X10D – U/UTP (Riser)         | B Outlet* – Dual Row Standard Density      | 2 Right Paired Flat     | 2 Right Paired Flat     |
| C Cat 6A X10D – U/UTP (LSZH)          | C Outlet* – Dual Row High Density          | 3 Right Series Flat     | 3 Right Series Flat     |
| D Cat 6A X10D – F/UTP (Plenum)        | G RJ45 Plug* – Single Row Standard Density | 4 Left Paired Flat      | 4 Left Paired Flat      |
| E Cat 6A X10D – F/UTP (Riser)         | H RJ45 Plug* – Dual Row Standard Density   | 5 Left Series Flat      | 5 Left Series Flat      |
| F Cat 6A X10D – F/UTP (LSZH)          | J RJ45 Plug* – Dual Row High Density       | 6 Trident Paired Flat   | 6 Trident Paired Flat   |
| G Cat 6 XL – U/UTP (Plenum)           | N 1100 Module                              | A Trident Series Angled | A Trident Series Angled |
| H Cat 6 XL – U/UTP (Riser)            | R 360 1100 Evolve Module                   | B Right Paired Angled   | B Right Paired Angled   |
| J Cat 6 XL – U/UTP (LSZH)             | S OneLink 2x6                              | C Right Series Angled   | C Right Series Angled   |
| Q Cat 6A X10D – S/FTP (LSZH)          | T OneLink 2x4                              | D Left Paired Angled    | D Left Paired Angled    |
| R Cat 6 – U/UTP Class B Rated (LSZH)  |  | E Left Series Angled    | E Left Series Angled    |
| S Cat 6A – U/UTP Class B Rated (LSZH) |  | F Trident Paired Angled | F Trident Paired Angled |
| Y Cat 6A X10D SD – U/UTP (Riser)      |  |                         | X Not Applicable        |

  

| Connector A                                | Link | Outlet Color     | UOM       | Length |
|--|------|------------------|-----------|--------|
| A Outlet* – Single Row Standard Density    | B 6  | 0 Not Applicable | 11 F Foot | 12 XXX |
| B Outlet* – Dual Row Standard Density      | C 8  | 1 Black (BK)     | M Meter   |        |
| C Outlet* – Dual Row High Density          | D 12 | 2 Blue (BL)      |           |        |
| G RJ45 Plug* – Single Row Standard Density | E 16 | 3 White (WH)     |           |        |
| H RJ45 Plug* – Dual Row Standard Density   | F 18 |                  |           |        |
| J RJ45 Plug* – Dual Row High Density       | G 24 |                  |           |        |
| N 1100 Module                              |      |                  |           |        |
| R 360 1100 Evolve Module                   |      |                  |           |        |
| S OneLink 2x6                              |      |                  |           |        |
| T OneLink 2x4                              |      |                  |           |        |
| X Unterminated                             |      |                  |           |        |

  

| Bundling      | Jacket Color | Labeling          |
|---------------|--------------|-------------------|
| H Hook-n-loop | 8 White (WH) | 8 A Generic Label |
| S Sleeving    | C Slate (SL) |                   |
|               | Z Blue (BL)  |                   |

- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
- Cords < 1m are also valid elements for use in a channel or as an equipment interconnect, but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |